



## PRO RECHARGEABLE FLOODLIGHTS | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

*One brand, endless solutions..*

SKU: 20038 - 930 1447

[View more details](#)

### TECHNICAL INFORMATION

Watts:	10
Lumens:	700
Input Power:	AC:100-240V
Long Life:	30,000 Hours
Unit Color:	Green+Black
Body Type:	Plastic
PF:	>0.9
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Operation Temperature:	-20°C to +45°C
Dimmable:	No
Beam Angle:	100°
Color:	4000K
Dimension:	175x125mm
Battery Type:	3.7V Li-Ion 3600mAh
No. Of Led:	16



### FEATURES

- Rechargeable floodlights with high quality LED Samsung chips
- High capacity battery (battery\_type) for long lifespan and higher charging cycles
- Built with On/Off switch
- Micro USB port for charging with LED Indicator for charging levels
- Designed with adjustable bracket (Max. 45°).
- Portable and easy to use
- Suitable for trekking camps, travellers, emergency operations etc.



### PACKAGING

Gross Weight (Kgs): 0.444  
 Unit CBM: 0.000975  
 Dimension: 175x125mm

### MASTER BOX PACKAGING

Box Qty: 20  
 Qty Per Pallet: 800  
 Length (Box) mm: 50  
 Width (Box) mm: 150  
 Height (Box) mm: 130

### LISTING DETAILS

Commodity Code: 9405403990  
 EanCode: 3800157653756