## 12VDC 2A UK Power Supply



TIGER PART: TP1005

## Features:

- Supplied with fixed UK pins
- Universal 100-240vac input voltage
- Level VI efficiency
- Approved to latest EN62368-1 safety standard
- CE marked and confirms with UKCA requirement



| Part number:           | TP1005                      |
|------------------------|-----------------------------|
| Input voltage:         | 100-240vac (90-264vac max.) |
| Input frequency:       | 47 - 63Hz                   |
| Output voltage:        | 12vdc                       |
| Current:               | 2000mA (2 amp)              |
| Power:                 | 24 Watts                    |
| Protection:            | Short Circuit, Over voltage |
| Dimensions:            | 59 x 48 x 29mm              |
| Cord length:           | 1.5 metres                  |
| DC connector:          | 2.1 x 5.5 x 12mm (Female)   |
| Polarity:              | +ve (positive) centre       |
| Leakage current:       | <0.25mA                     |
| Operating temperature: | 0°C to + 40°C               |


## TIGER POWER PRODUCTS - QUALITY & RELIABILITY

This specification is not for general release or circulation. Tiger Power reserves the right to make changes to spec. or product without notice or liability.

## 12VDC 2A UK Power Supply



TIGER PART: TP1005



This specification is not for general release or circulation. Tiger Power reserves the right to make changes to spec. or product without notice or liability.