

# Panel Mount Plug

## 3 Way


**multicomp**PRO



### Specifications:

Waterproof Rate	: IP67
IP67	: Immersed in 1m water for 30 minutes
Temperature Range	: -40°C to +100°C
Current Rating	: 10A
Dielectric withstanding Voltage	: 1,000V AC for one minute
To Conform to Hazardous Substance free Spec.	
Green Product to Identification Label on Packaging	
For Panel Thickness max of 4mm	

### Diagram



No	Description	Qty	Material	Plating & Colour
A	Body	1	Nylon + GF	Black
B	Female Pin	3	Phosphor Bronze Alloy	1μ" Gold Plating over Nickel Plating
C	Gasket	1	EPDM	Black
D	Nut	1	Nylon + GF	Black
E	Liquid Glue	1		Black

### Part Number Table

Description	Part Number
Socket, Panel, 10A, 3 Way, IP67	2CT3014-W03400

Dimensions : Millimetres

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
Element14.com/multicomp-pro

**multicomp**PRO