

Han-Eco 24B-HBM/RA-with SL-with cover



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 19 43 024 0331 |
| Specification | Han-Eco 24B-HBM/RA-with SL-with cover |
| HARTING eCatalogue | https://b2b.harting.com/19430240331 |

Identification

| | |
|-----------------------------|--|
| Category | Hoods/Housings |
| Series of hoods/housings | Han-Eco® B |
| Type of hood/housing | Bulkhead mounted housing |
| Description of hood/housing | With thermo-plastic cover Rear mounting |

Version

| | |
|--------------|--------------------------------|
| Locking type | Single locking lever |
| Size | 24 B |
| Details | Please order frame separately. |

Technical characteristics

| | |
|--|-----------------|
| Limiting temperature | -40 ... +125 °C |
| Number of relockings | ≥500 |
| Degree of protection acc. to IEC 60529 | IP66 |

Material properties

| | |
|---|--|
| Material (hood/housing) | Polyamide (PA) Fibre-glass reinforced |
| Colour (hood/housing) | RAL 9005 (jet black) |
| Material (locking) | Polyamide (PA) Fibre-glass reinforced |
| Colour (locking) | RAL 9005 (jet black) |
| Material flammability class acc. to UL 94 | V-0 |



Pushing Performance

Material properties

Material flammability class acc. to UL 94
(locking levers) V-0

RoHS compliant

ELV status compliant

China RoHS e

REACH Annex XVII substances No

REACH ANNEX XIV substances No

REACH SVHC substances No

Specifications and approvals

Specifications IEC 61984
EN 45545-2 R22: HL1, HL2, HL3
EN 45545-2 R23: HL1, HL2, HL3
EN 45545-2 R24: HL1, HL2, HL3

Commercial data

Packaging size 1

Country of origin Germany

European customs tariff number 85389099

eCl@ss 27440202 Shell for industrial connectors