

## Han-Eco 10B Outd.-HSM1-f. DL-M32-cov.-gl



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                                       |
|--------------------|---------------------------------------------------------------------------------------|
| Part number        | 19 43 310 0227                                                                        |
| Specification      | Han-Eco 10B Outd.-HSM1-f. DL-M32-cov.-gl                                              |
| HARTING eCatalogue | <a href="https://b2b.harting.com/19433100227">https://b2b.harting.com/19433100227</a> |

### Identification

|                             |                                                          |
|-----------------------------|----------------------------------------------------------|
| Category                    | Hoods/Housings                                           |
| Series of hoods/housings    | Han-Eco <sup>®</sup> B                                   |
| Type of hood/housing        | Surface mounted housing                                  |
| Description of hood/housing | With thermo-plastic cover<br>With integrated cable gland |

### Version

|              |                                    |
|--------------|------------------------------------|
| Locking type | Double locking lever (on the hood) |
| Size         | 10 B                               |
| Version      | Side entry                         |
| Cable entry  | 1x M32                             |

### Technical characteristics

|                                        |                 |
|----------------------------------------|-----------------|
| Limiting temperature                   | -40 ... +125 °C |
| Number of relockings                   | ≥500            |
| Degree of protection acc. to IEC 60529 | IP66            |
| Clamping range                         | 13 ... 21 mm    |

### Material properties

|                         |                                          |
|-------------------------|------------------------------------------|
| Material (hood/housing) | Polyamide (PA)<br>Fibre-glass reinforced |
| Colour (hood/housing)   | RAL 9005 (jet black)                     |
| Material (seal)         | FPM                                      |
| Colour (seal)           | RAL 7001 (silver-grey)                   |



Pushing Performance

## Material properties

|                                           |     |
|-------------------------------------------|-----|
| Material flammability class acc. to UL 94 | V-0 |
|-------------------------------------------|-----|

## Specifications and approvals

|                |                               |
|----------------|-------------------------------|
| Specifications | IEC 61984                     |
|                | EN 45545-2 R22: HL1, HL2, HL3 |
|                | EN 45545-2 R23: HL1, HL2, HL3 |
|                | EN 45545-2 R24: HL1, HL2, HL3 |
| CE             | Yes                           |

## Commercial data

|                                |                                          |
|--------------------------------|------------------------------------------|
| Packaging size                 | 1                                        |
| Country of origin              | Germany                                  |
| European customs tariff number | 85389099                                 |
| eCl@ss                         | 27440202 Shell for industrial connectors |