



TE Internal #: T4051410003-004

M8/M12 Cable Assemblies, Sensor/Actuator, 3 Positions, A M8 /M12 Cable Assembly Keying, Receptacle, M8 Pigtail, Cable Assembly Length 3000 mm

[View on TE.com >](#)

Cable Assemblies > Copper Cable Assemblies > M8/M12 Cable Assemblies > M8 FEMALE R/A SINGLE ENDED CABLE ASSY



M8/M12 Application Type: **Sensor/Actuator**

Number of M8/M12 Cable Assembly Positions: **3**

M8/M12 Cable Assembly Keying: **A**

M8/M12 Cable Assembly Connector Type: **Receptacle**

M8/M12 Cable Assembly Type: **M8 Pigtail**

All M8 FEMALE R/A SINGLE ENDED CABLE ASSY (56)

Features

Product Type Features

LED	Without
Cable Type	PVC
Product Type	Cable Assembly
Assembly Type	Pigtail
M8/M12 Cable Assembly Connector Type	Receptacle
M8/M12 Cable Assembly Type	M8 Pigtail
M8/M12 Cable Assembly Shielded	No

Configuration Features

Number of M8/M12 Cable Assembly Positions	3
M8/M12 Cable Assembly Keying	A
M8/M12 Cable Assembly Configuration	Single Ended

Electrical Characteristics

Operating Voltage	60 VAC
-------------------	--------



Body Features

Wire Color	Brown, Blue, Black
Cable Exit Angle	Right Angle
Environmental Protection	With
Insulation Material	PUR
Conductor Material	Copper Alloy
Cable Jacket Color	Black

Contact Features

Contact Current Rating	3 A
------------------------	-----

Mechanical Attachment

Screw & Hole Thread Size	M8
--------------------------	----

Housing Features

M8/M12 Cable Assembly Housing Material	Nylon
----------------------------------------	-------

Dimensions

Wire Size	.25 mm <sup>2</sup>
Cable Assembly Length	3000 mm

Operation/Application

M8/M12 Application Type	Sensor/Actuator
-------------------------	-----------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUN 2020 (209) Candidate List Declared Against: JAN 2020 (205) SVHC > Threshold: Pb (1.9% in Pb-Alloy in Copper) <b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-SE594-M1C M8 MALE R/A PIGTAIL	TE Part # CAT-SE594-M1O M8 MS-FR LED DOUBLE ENDED CABLE	TE Part # CAT-SE594-M1B M8 MALE R/A SINGLE ENDED CABLE ASSY	TE Part # CAT-SE594-M1U M8 MR -M12 FS CABLE ASSEMBLY

Customers Also Bought

TE Part #T1620063120-000 H6B-SDR-M20	TE Part #T1620163125-000 H16B-SDR-LB-M25	TE Part #T1310160125-000 H16B-TS-RO-M25	TE Part #T1430160000-000 H16B-AD-BO
TE Part #T1310060120-000 H6B-TS-M20	TE Part #T1230240121-000 H24B-TSH-PG21	TE Part #T2050462201-000 HEE-046-F	TE Part #T2050462101-000 HEE-046-M



Documents

Product Drawings

M8 CABLE RA FEMALE 3M 3P PVC CABLE

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_T4051410003-004\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_T4051410003-004\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_T4051410003-004\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

M8 / M12 Connector System Catalog

English

Product Specifications

Application Specification

English