

2m (6 ft) Certified SuperSpeed USB 3.0 A to B Cable - M/M

Product ID: USB3CAB2M



The USB3CAB2M 2-meter USB 3.0 A-to-B cable provides a high quality connection between peripheral devices that feature a USB 3.0 type-B port, such as hard drive enclosures, card readers, docking stations and video capture devices and a USB-capable computer.

This cable is USB-IF certified to USB 3.0 specifications, guaranteeing a dependable, long-lasting connection to your USB 'B' devices and is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Connect a SuperSpeed USB 3.0 Type B peripheral (hard drive enclosure, card reader, docking station, video capture device, etc.) to a USB 3.0 capable desktop, laptop, or server

Features

- 1x USB 'A' male connector
- 1x USB 'B' male connector
- Data transfer rates up to 5Gbps
- Aluminum-Mylar Foil with Braided Shielding
- Molded connectors with strain relief
- Backward compatible with USB 2.0

- USB-IF Certified SuperSpeed USB 3.0

Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Type and Rate	USB 3.0 - 5 Gbit/s
---------------	--------------------

Connector(s)

Connector A	USB Type-A (9 pin) USB 3.0 (5 Gbps)
Connector B	USB Type-B (9 pin) USB 3.0

Environmental

Operating Temperature	-20C to 80C (-4F to 176F)
Storage Temperature	-20C to 80C (-4F to 176F)

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	24/28 AWG
Cable Length	6.6 ft [2 m]
Product Length	6.6 ft [2 m]
Weight of Product	3.2 oz [90 g]

Packaging Information

Package Quantity	1
Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]



Package Height 0.6 in [16 mm]

Shipping (Package) Weight 3.5 oz [99 g]

What's in the Box

Included in Package 2m USB 3.0 Certified A to B Cable - M/M

****Product appearance and specifications are subject to change without notice.***

