



Quality Products. Service Excellence.

GR-63-CORE Zone 4 Seismic Server Cabinet *DCZ4 Series*

UL 2416 Rated 3,000 lbs (1,361 kg) Weight Capacity



Features

- Rugged design that is engineered to perform in the most critical seismic environments.
- Includes generous stud locations for grounding and bonding applications.
- Cable management includes
 - Four (4) 3.5" top cable access holes.
 - Various bottom panels allow for different cable management options.
 - Corner braces include mounting for cable tray and outlet strips.
 - Support for up to four optional 4" deep vertical cable managers.
- Ganging holes allow for joining multiple cabinets.
- C-channel struts provide cabinet strength, ease and flexibility to adjust mounting rails.
- Flush-mount doors come with 3-point latching and stiffeners to reduce flexing and bowing while increasing cabinet security.



Tested by



ZONE⁴
SEISMIC



Specifications

- Cabinet frame constructed in 14-gauge steel cabinet with 12-gauge steel re-enforced corner brackets.
- Cabinet doors and side panels constructed in 16-gauge steel.
- Includes two (2) pairs of EIA compliant square hole mounting rails with rack unit markings.
 - Mounting rails are constructed in 12-gauge steel, and are Zinc-plated to provide superior surface areas for equipment grounding.
- Dynamic (seismic) load rated up to 1,000 lb. (454 kg) of equipment installed and 100 lb. (45 kg) of cable weight on the top. Requires a seismic bolt down kit such as the **C4K-Z4** (sold separately). Independently tested and certified to exceed established Seismic Zone 4 NEBS™ Telcordia® GR-63-CORE testing standards.
- UL Listed 2416 load rated for up to 3,000 lbs (1,360 kg). Static Load tested to 12,000 lbs (5,443 kg).
- Grounding studs bonded to frame, side panels and doors. Front and rear studs on cabinet frame conform to PET.
- Finished in textured black powder paint. Also available in textured white upon request.
- TAA compliant for GSA Schedule purchases.
- RoHS Compliant.
- Manufactured in North America.

Included Components

- Steel frame which includes nylon leveling feet, recessed casters and grounding studs.
- Two (2) pairs of infinitely adjustable 19" EIA compliant square hole punched rails with rack unit markings.
- Two (2) perforated front door (63% open area vented) with locking swing-handle.
- Two (2) removable solid side panels.
- One (1) removable solid top panel.

Gallery



Accessories

- Vertical Cable Manager with Door
- Four Post Fixed Depth Shelf
- Adjustable Depth Shelf
- Rack Mount Locking Storage Drawer
- PDUs and Outlet Strips
- Adjustable Depth Cable Manager
- Horizontal Ring Cable Manager
- Horizontal Steel Finger Cable Manager
- Cabinet Top Panels
- Mounting Hardware
- Grounding & Bonding
- Universal Rack Shelf
- Four Post Mounting Zero Space Fixed Shelf
- Four Post Mounting Sliding Shelf
- Sliding Keyboard Shelf
- Rack Unit Label
- Horizontal Lacing Strip
- Horizontal Hinged Cable Manager
- Cable Management Arm
- Vertical Cable Tray
- Rack Panels

Part No.	Overall Dimensions			Rack Units	Usable Mounting Dimensions		
	Height	Width	Depth		Height	Width	Depth
DCZ4A307742BK	82.81	30.00	42.00	44U	77.06	19.00	35.75

Comes complete with all components assembled.

Overall height includes leveling feet.

Optional Doors

Part No.	Part No.	Part No.
Solid Door	Window Door	63% Vented Door
DCZ4SD3077BK	DCZ4WD3077BK	DCZ4VD3077BK

Tags: **sismic**

Data subject to change without notice

© 2021. Hammond Manufacturing Ltd. All rights reserved.