




*Quality Products. Service Excellence.*


## Two Post Centered Shelf *DNDM Series*

200 lbs (91 kg) Weight Capacity

### Features



- 16-gauge steel construction.
- The vented version provides a sturdy shelf without obstructing upward heat movement.
- Front & rear lip folded for extra strength & become equipment retainers.
- Rugged textured black powder paint finish.
- Solid version available in either 19" or 23" rack panel width.
- Tested to nearly double the suggested load rating of 200 lbs (91 kg).
- Finished in textured black powder paint.
- TAA Compliant
- RoHS and REACH compliant.
- Manufactured in North America.



### Accessories

- Mounting Hardware
- Hook and Loop Roll



### 19" Mounting

Part No.	Part No.	Overall Dimensions		Rack	Mounting
Vented	Solid	Height	Depth	Units	Width
-	DNDMS1916BK1	3.50	16.00	2U	19.00
DNDMV1918BK1	DNDMS1918BK1	3.50	18.00	2U	19.00
DNDMV19BK1	DNDMS19BK1	3.50	19.50	2U	19.00
-	DNDMS1920BK1	3.50	20.00	2U	19.00
-	DNDMS1922BK1	3.50	22.00	2U	19.00
-	DNDMS1924BK1	3.50	24.00	2U	19.00

### 23" Mounting

Part No.	Overall Dimensions		Rack	Mounting
Solid Only	Height	Depth	Units	Width
DNDMS23BK1	3.50	19.50	2U	23.00

*Data subject to change without notice*

