

# CAMBLOCK PLUS

## 3.81mm Pitch Pluggable Screwless Terminal Block

PCB  
TERMINAL  
BLOCKS

- 2-12 pole solid block
- Screwless connectivity
- Pluggable male-female connectors
- Polarised mouldings
- 0.1 - 0.5mm<sup>2</sup> (26-21AWG) solid and stranded cable
- Moulded in green UL94-V0 flame retardant PA66
-  approved

### SPECIFICATION

Rating	UL=8A/300V, IEC=10A/250V
Insulation resistance	500MΩ/500V
Withstand voltage	AC2000V/1min
Contact resistance	20mΩ (max)
Working temperature	-40°C to +105°C
Mouldings	UL94-V0, flame retardant PA66
Spring	Stainless steel
Contact	Bronze, Ni plated

TYPE NO.	POLES	LENGTH
CSTBP92HE/2	2	8.41mm
CSTBP92HE/3	3	12.22mm
CSTBP92HE/4	4	16.03mm
CSTBP92HE/5	5	19.84mm
CSTBP92HE/6	6	23.65mm
CSTBP92HE/7	7	27.46mm
CSTBP92HE/8	8	31.27mm
CSTBP92HE/9	9	35.08mm
CSTBP92HE/10	10	38.89mm
CSTBP92HE/11	11	42.7mm
CSTBP92HE/12	12	46.51mm

CSTBP92HE

