

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1727673008

Status:

Active

Overview:

Description:

Mini-Fit Sigma Plug Housing, 4.20mm Pitch, Dual Row, Panel Mount, UL 94V-0, Glow-Wire Capable, 8 Circuits

General	
Product Family	Crimp Housings
Series	172767
Application	Power, Wire-to-Board, Wire-to-Wire
Overview	minifit_power_connector_solutions
Product Name	Mini-Fit Sigma
UPC	193264446483
Physical	
Circuits (maximum)	8
Color - Resin	Black
Gender	Plug
Glow-Wire Capable	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	3.030/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Application Specification	2131370000-AS-000
Packaging Specification	1727670002-PK-000
Product Specification	2029880002-PS-000, 2131370000-PS-000
Sales Drawing	1727670002-SD-000
Test Summary	2131370002-TS-000

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - D(2020)9139-DC (19 Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

172767 Series

Mates With

Mini-Fit Sigma Receptacle Housing

1727081008

Use With

Mini-Fit TPA2/Sigma Male Terminal

172765 , 203070 . Mini-Fit Sigma Retainer

1727092004

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION