



## **PRODUCT DATA SHEET**

Part Number: 195A135X

Туре	Size	Rating	Description	
LED	M22	24Vac/dc	Standard Bezel Panel Indicator	





Part #	Colour	Current (mA)	Intensity (mcd)
195A1350	Red	16	160
195A1351	Green	16	400
195A1352	Yellow	16	350
195A1357	Blue	16	280
195A135WA	White	16	900

## Notes:

- 1 Electrical & optical data are measured at an ambient temperature of 25°C
- 2 Storage temperature -25 °C to +80°C
- 3 Application temperature -20 °C to +60°C
- 4 Voltage tolerance ±10%
- 5 Due to component tolerances, colour temperature variations may be observed
- 6 The terminals are not qualified for soldering
- 7 Degree of protection IP67 when used with the supplied gasket
- 8 The plastic(polycarbonate) has limited chemical resistance
- 9 RoHS & REACH SVHC compliant