


PRODUCT DATA SHEET

Part Number: 1905X05X

Туре	Size	Description		
LED	M8	LED Recessed Panel Indicator with terminals		



Part #	Colour	V_{f}	Current (mA)	Intensity (mcd)
1905X053	Red	2.0	20	50
1905X051	Green	2.0	20	40
1905X052	Yellow	2.1	20	40
1905X058	Orange	2.0	20	55

Notes:

- 1 X=bezel chrome finish, 0=Satin, 1=Black, 2=Matt
- 2 Electrical & optical data are measured at an ambient temperature of 25°C
- 2 Storage temperature -25 °C to +80°C
- 3 Application temperature -20 °C to +60°C
- 4 Terminal polarity: brass positive
- 5 IP67 sealed with the fitted gasket
- 6 Due to component tolerances, colour temperature variations may be observed
- 7 The plastic (polycarbonate) has limited chemical resistance
- 8 RoHS & REACH SVHC compliant