

BNC Male Crimp to BNC Male Crimp R/A

multicompPRO


**RoHS
Compliant**



Specifications

Connector to Connector : 90° BNC Plug to BNC Plug
Coaxial Cable Type : RG58A
Impedance : 50Ω
Jacket Colour : Black

Diagram



Part Number Table

Description	Cable Type	Strain Relief	Length (Inches)	Part Number
Cable Assembly BNC Male Crimp to BNC Male Crimp R/A	RG-59B/U	No	24	SPC20685
	RG-59B/U	No	72	SPC20686
	RG-58A/U	Yes	12	SPC20687
	RG-58A/U	Yes	24	SPC20688
	RG-58A/U	Yes	36	SPC20689
	RG-58A/U	Yes	48	SPC20690
	RG-58A/U	Yes	72	SPC20691
	RG-58C/U	No	36	SPC20692
	RG-58C/U	No	72	SPC20693
	LMR-195	No	60	SPC20753
	LMR-196	No	72	SPC20754

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicompPRO