

Banner's Call for Parts creates a steady workflow and pinpoints critical issues. [Learn more.](#)

SXA-1715D

► SINGLE-ENDED CORDSETS



Euro-Style Quick Disconnect Cable
17 Pin Euro-Style Female Connector
5 m (15 ft) in Length
Non-Shielded
Part Number: 810447

SPECIFICATIONS

Number of Contacts	17
Number of Connectors	1
Cable Jacket Material	PUR
Cable Jacket Color	Black
Connector Body Material/Color	PUR Black
Outside Cable Diameter (mm)	7
Cordset Length (m)	4570
Trunk Length (m)	No Trunk
Shield/No Shield	No Shield
Coupling Material/Color	Nickel Plated Brass
Maximum Temp. (°C)	80
Current Rating (A)	1.0

Offline (Contact Us)

Minimum Temp. (°C)	-40
Voltage Rating (V)	75 V ac/dc
IP Rating	IP67
Primary Connector Type	EURO
Primary Coupling Method	M12 Single Key
Primary Gender	Female
Primary Orientation	Straight
Primary Number of Conductors	17
Primary AWG	26, 28
Secondary Connector Type	Flying Leads
Secondary Number of Conductors	17
Secondary AWG	26, 28
Feature: Hazardous Area	No
Oil/Grease Resistant	No



Banner Engineering Corp. | 9714 Tenth Avenue North | Minneapolis, MN 55441 | United States of America