

PREMIUM Series



Roebuck

Bi-component handles enables comfortable and efficient force transmissions. The hole in the handle permits the insertion of a T bar for added force and for hanging on a tool-board after use. The chrome-molybdenum vanadium blade combines great hardness and toughness which guarantees optimum performance.

7 piece set available containing:

Flared Tip	125 x 65	125 x 4.0	Pozidriv	No. 1
	150 x 8.0	150 x 5.5		No. 2
Parallel Tip	100 x 3.0			

233058

	Blade Length	Tip Size	Order Code	Price Each
	Slotted, Flared Tip			
	100	5.5 × 1.0mm	385-8108	
	150	8.0 × 1.2mm	385-8110	
	200	10.0 × 1.6mm	385-8121	
	250	12.0 × 2.0mm	385-8133	
	25 Stubby	6.0 × 1.0mm	385-8145	
	Slotted, Parallel Tip			
	75	3.0 × 0.5mm	385-8157	
	100	3.0 × 0.5mm	385-8169	
	200	3.0 × 0.5mm	385-8170	
	125	4.0 × 0.8mm	385-8182	
	250	4.0 × 0.8mm	385-8194	
	150	5.5 × 1.0mm	385-8200	
	300	5.5 × 1.0mm	385-8212	
	150	6.5 × 1.2mm	385-8224	
	300	6.5 × 1.2mm	385-8236	
	Phillips			
	75	No.0	385-8248	
	100	No.1	385-8250	
	125	No.2	385-8261	
	300	No.2	385-8273	
	150	No.3	385-8285	
	25 Stubby	No.2	385-8303	
	Pozidriv			
	75	No.0	385-8315	
	100	No.1	385-8327	
	125	No.2	385-8339	
	150	No.3	385-8340	
	200	No.4	385-8352	
	Torx			
	75	T6	385-8364	
	75	T7	385-8376	
	75	T8	385-8388	
	75	T9	385-8390	
	75	T10	385-8406	
	100	T15	385-8418	
	100	T20	385-8420	
	125	T25	385-8431	
	125	T27	385-8443	
	150	T30	385-8455	
	150	T40	385-8467	
	Set			
	7 piece		385-8479	