

60.251.11 ✓ ACTIVE

TE Internal #: 60-0251-011-000

Standard Circular Connectors, 14A Contact Current Rating (Max), Power, Brass, 15 Shell Size, 0° Alignment Keyed, Metal, Socket

[View on TE.com >](#)



Connectors > Circular Connectors > Standard Circular Connectors



Sealable: **No**

Contact Current Rating (Max): **14 A**

Circuit Application: **Power**

Shell Base Material: **Brass**

Circular Connector Shell Size: **15**

Features

Product Type Features

Sealable	No
Shell Type	Metal

Body Features

Shell Base Material	Brass
---------------------	-------

Contact Features

Contact Current Rating (Max)	14 A
Circular Connector Contact Type	Socket

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Housing Features

Circular Connector Shell Size	15
Alignment Keyed	0°

Operation/Application

Durability Rating	500 Cycles
-------------------	------------

Circuit Application

Power

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	<p>Current ECHA Candidate List: JUN 2020 (209)</p> <p>Candidate List Declared Against: JUN 2020 (209)</p> <p>SVHC > Threshold:</p> <p>Pb (1.5% in Component)</p> <p>Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</p>
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts







TE Part # C0-0258-000-000
POSITIONING INSERT FOR 1 MM CONTACTS



TE Part # C0-0201-000-000
CRIMPING TOOL MID-SIZE




TE Part # C0-0235-000-000
DIGITAL CRIMPING TOOL, SMALL



TE Part # ESB205N00320003000
915 PLUG



TE Part # ESA205N00320003000
915 PLUG



TE Part # ESA205N00310003000
915 plug

Customers Also Bought



TE Part #1879350-1
RR01 5% R22 AMMO



TE Part #2842142-7
14P, 2MM, BRK HDR, DRVT, SMD, 0.1AU, TR W/CAP



TE Part #4-1625827-2
Metal Chip Resistor: Current Sense



TE Part #4-1462039-1
IM STANDARD (2 FORM C, 2CO CONTACTS)



TE Part #6-2176360-3
RQ 0402 1K91 0.1% 10PPM 1K RL



TE Part #ESA202N00340500000
915 PLUG



TE Part #1-1462052-9
HF6 95=50OHM140MW 9V BIST 2COIL



TE Part #61-0231-011-000
CONTACT PIN 1 MM



TE Part #60-0252-011-000
CONTACT SOCKET 1 MM



TE Part #1879262-8
RP 2B 13K7 0.1% 15PPM 1K RL

Documents



CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_60-0251-011-000_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_60-0251-011-000_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_60-0251-011-000_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Socket 1mm 60.251.11

English