

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0348948009](#)  
**Status:** **Active**  
**Overview:** [Mini50 Connection Systems](#)  
**Description:** Mini50 Sealed Receptacle Housing, Dual Row, without CPA, 16 Circuits, Polarization Option A, Black

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Test Summary 349670001-TS-000 (PDF)</a>
<a href="#">Product Specification 349670001-000 (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Application Specification 348940001-AS-CH-000 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Application Specification AS-34894-0001-001 (PDF)</a>	

**General**

Product Family	Crimp Housings
Series	<a href="#">34894</a>
Application	Automotive, Power, Sealed, Wire-to-Board
Overview	<a href="#">Mini50 Connection Systems</a>
Polarization	A
Product Name	Mini50 Sealed
UPC	191128407472

**Physical**

Circuits (maximum)	16
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	8.046/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.80mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C, -40° to +125°C

**Material Info**

**Reference - Drawing Numbers**

Application Specification	348940001-AS-CH-000, AS-34894-0001-001
Product Specification	349670001-000
Sales Drawing	347350050-000, 348940001-000, 348950800-000
Test Summary	349670001-TS-000



**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Not Relevant

Compliant

Not Contained

**Search Parts in this Series**

[34894 Series](#)

**Use With**

CTX50 Sealed Receptacle Terminal [34905](#)