

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0348948001](#)
Status: **Active**
Overview: [Mini50 Connection Systems](#)
Description: [Mini50 Sealed Receptacle Housing, Dual Row, with CPA, 16 Circuits, Polarization Option A, Black](#)

Documents:

Drawing (PDF)	Test Summary 349670001-TS-000 (PDF)
Product Specification 349670001-000 (PDF)	Datasheet (PDF)
Application Specification 348940001-AS-CH-000 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-34894-0001-001 (PDF)	

General

Product Family	Crimp Housings
Series	34894
Application	Automotive, Power, Sealed, Wire-to-Board
Overview	Mini50 Connection Systems
Polarization	A
Product Name	Mini50 Sealed
UPC	191128407373

Physical

Circuits (maximum)	16
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	8.046/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.80mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C, -40° to +125°C

Material Info

Reference - Drawing Numbers

Application Specification	348940001-AS-CH-000, AS-34894-0001-001
Product Specification	349670001-000
Sales Drawing	347350050-000, 348940001-000, 348950800-000
Test Summary	349670001-TS-000



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

[34894 Series](#)

Use With

[CTX50 Sealed Receptacle Terminal 34905](#)