

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2125201010](#)
Status: **Active**
Overview: [Mini-Fit Family Power Connectors](#)
Description: Mini-Fit Max Vertical Header, Dual Row, 10 Circuits, Tin (Sn) Plating, Black

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family PCB Headers
Series [212520](#)
Application Power, Wire-to-Board
Overview [Mini-Fit Family Power Connectors](#)
Product Name Mini-Fit Max
UPC 193264595549

Physical

Breakaway No
Circuits (Loaded) 10
Circuits (maximum) 10
Color - Resin Black
Durability (mating cycles max) 30
First Mate / Last Break No
Glow-Wire Capable Yes
Guide to Mating Part No
Keying to Mating Part Yes
Lock to Mating Part Yes
Material - Metal Copper Alloy
Material - Plating Mating Tin
Material - Resin Liquid Crystal Polymer
Net Weight 2.830/g
Number of Rows 2
Orientation Vertical
PCB Locator Yes
PCB Retention Yes
PCB Thickness - Recommended 1.60mm
Packaging Type Tray
Pitch - Mating Interface 4.20mm
Pitch - Termination Interface 4.20mm
Polarized to Mating Part Yes
Polarized to PCB Yes
Shrouded Fully
Temperature Range - Operating -40° to +105°C
Termination Interface: Style Through Hole

Electrical

Current - Maximum per Contact 20.0A
Voltage - Maximum 600V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Sales Drawing 2125200001-SD-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[212520](#) Series

Mates With

Mini-Fit Max Crimp Housing [212514](#)