

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2163301044](#)  
**Status:** **Active**  
**Overview:** [Off-the-Shelf Cable Assemblies](#)  
**Description:** EdgeLock-to-EdgeLock Off-the-Shelf (OTS) Cable Assembly, 2.00mm Pitch, Tin (Sn) Plating, 600.00mm Length, 4 Circuits, Black

**Documents:**

[Drawing \(PDF\)](#) [Datasheet \(PDF\)](#)  
[Packaging Specification 2163301021-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

|                        |  |
|------------------------|--|
| Product Family         | Cable Assemblies                               |
| Series                 | <a href="#">216330</a>                         |
| Application            | Signal, Wire-to-Board                          |
| Assembly Configuration | Dual Ended Connectors                          |
| Connector to Connector | Edgelock-to-Edgelock                           |
| Overview               | <a href="#">Off-the-Shelf Cable Assemblies</a> |
| Product Name           | EdgeLock                                       |
| Type                   | Discrete Wire Assembly                         |
| UPC                    | 193264682836                                   |

**Physical**

|                                |  |
|--------------------------------|--|
| Cable Length                   | 600.00mm                                       |
| Circuits (Loaded)              | 4  |
| Color - Resin                  | Black  |
| Gender                         | N/A  |
| Material - Metal               | Phosphor Bronze                                |
| Material - Plating Mating      | Tin  |
| Material - Plating Termination | Tin  |
| Material - Resin               | Nylon  |
| Net Weight                     | 14.267/g                                       |
| Packaging Type                 | Bag  |
| Pitch - Mating Interface       | 2.00mm   |
| Plating min - Mating           | 1.000µm  |
| Single Ended                   | No   |
| Termination Interface: Style   | Crimp or Compression, Straddle Mount-Edge Card |
| Wire Insulation Diameter       | 1.10-1.40mm                                    |
| Wire Size AWG                  | 22   |
| Wire/Cable Type                | UL 10002                                       |

**Electrical**

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 3.0A |
| Voltage - Maximum             | 125V |

**Material Info**

**Reference - Drawing Numbers**

|                         |                |
|-------------------------|----------------|
| Packaging Specification | 2163301021-001 |
| Sales Drawing           | 2163301041-000 |



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)9139-DC (19  
Jan 2021)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[216330 Series](#)