

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2160111021](#)
Status: **Active**
Overview: Super Sabre Connector System
Description: Super Sabre-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Single Row, 150.00mm Length, 2 Circuits, Black

Documents:

[Drawing \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|------------------------|-------------------------------------|
| Product Family | Cable Assemblies |
| Series | 216011 |
| Application | Power, Wire-to-Board, Wire-to-Wire |
| Assembly Configuration | Single Ended Connector |
| Connector to Connector | Super Sabre-to-Pigtail |
| Overview | <u>Super Sabre Connector System</u> |
| Product Name | Super Sabre |
| Type | Discrete Wire Assembly |
| UPC | 193264830510 |

Physical

| | |
|--------------------------------|-------------------|
| Cable Length | 150.00mm |
| Circuits (Loaded) | 2 |
| Color - Resin | Black |
| Gender | Female-Pigtail |
| Lock to Mating Part | Yes |
| Material - Metal | Copper |
| Material - Plating Mating | Silver |
| Material - Plating Termination | Matte Tin, Nickel |
| Material - Resin | Nylon |
| Net Weight | 22.610/g |
| Number of Rows | 1 |
| Pitch - Mating Interface | 7.50mm |
| Single Ended | Yes |
| Wire Size AWG | 10 |
| Wire/Cable Type | UL 11028 |

Electrical

| | |
|-------------------------------|-------|
| Current - Maximum per Contact | 34.0A |
|-------------------------------|-------|

Material Info

Reference - Drawing Numbers

| | |
|---------------|----------------|
| Sales Drawing | 2160111021-000 |
|---------------|----------------|



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[216011 Series](#)