

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2178422122](#)
Status: **Active**
Overview: [Off-the-Shelf Pre-Crimped Leads](#)
Description: Pre-Crimped Lead Mizu-P25 Male-to-Mizu-P25 Male, Tin (Sn) Plating, 150.00mm Length, 20 AWG, Red

Documents:

[Drawing \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	217842
Application	Signal, Wire-to-Wire
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Mizu-P25 Crimp Terminals
Overview	Off-the-Shelf Pre-Crimped Leads
Product Name	Mizu-P25
Type	Discrete Wire Assembly
UPC	195842150027

Physical

Cable Length	150.00mm
Circuits (Loaded)	1
Color - Resin	Red
Gender	Male-Male
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.193/g
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.40-1.90mm
Wire Size AWG	20
Wire/Cable Type	UL 10002

Electrical

Voltage - Maximum	125V
-------------------	------

Material Info

Reference - Drawing Numbers

Sales Drawing	2178421121-000
---------------	----------------



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[217842 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION