multicomp PRO




Specifications

Connector Type Connector Body Style Coaxial Termination Impedance Coaxial Cable Types Contact Material Contact Plating Connector Mounting

- : N Coaxial
- : Straight Plug
- : Solder
- : 50Ω
- : RG213
- : Brass
- : Silver Plated Contacts
- : Cable Mount





No.	Description	Material	Finish	
1	Centre Contact	Brass	Silver 70µ″ Min.	
2	Gasket	Silicone	None	
3	Shell	Brass	Silver 70µ″ Min.	
4	Washer	DIASS	None	
5	Insulation	PTFE	none	
6	Sleeve	Brass	Silver 70µ″ Min.	
7	Gasket	Silicone	None	
8	Body	Brass	Silver 70µ″ Min.	
9	Nut	DIASS		

Part Number Table

	Description	Part Number
Dimensions : Millimetres (Inches)	N Coaxial, Straight Plug, Solder, 50Ω, RG213, Brass	MP-11-01B-17 TSS

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

