

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0733000080**
Status: **Active**
Overview: SMPM and SMP RF Connectors
Description: 50 Ohms, SMPM Plug, PCB Mount, Vertical, Full Detent, 80 Pieces Per Tray

Documents:

Drawing (PDF)	HFSS Model
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
3D Model	

General

Product Family	RF/Coax Connectors
Series	73300
Overview	SMPM and SMP RF Connectors
Product Name	SMPM
Style	PCB
Type	Microminiature
UPC	884982495425
Wire/Cable Type	N/A

Physical

Gender	Plug
Keying to Mating Part	N/A
Net Weight	0.282/g
Orientation	Straight
PCB Mounting	Surface Mount
Packaging Type	Tray
Panel Mount	No
Panel Mount Method	N/A
Reverse Polar	No

Electrical

Frequency	26.5 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 217 Vrms@Sea Level


Solder Process Data

Duration at Max. Process Temperature (seconds)	010
Lead-freeProcess Capability	REFLOW
Max. Cycles at Max. Process Temperature	002
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-73300-008-001
---------------	------------------



EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per -
D(2020)9139-DC (19
Jan 2021)
lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

50 Image

Not Relevant

Not Contained

Search Parts in this Series

[73300 Series](#)