


PRODUCT SPECIFICATION

Brand	Kasp
Product Range	Hasp and Staples
Catalogue number	210
Date	15/03/2007

Range Description Traditional Hasp & Staples				
Features <ul style="list-style-type: none"> • Hardened staple – Extra protection from attack • Chrome plated finish – extra resistance to corrosion • Concealed fixings – added security <p>These Hasp and staples are supplied display packed in sealed blisters or boxed</p> <p>Fixing screws are included</p>				
Item Number	Item Description	EAN No	Commodity code	Carton Qty
K21075	Traditional hasp & staple 75mm – boxed	5013969902587	83024100	6
K21075D	Traditional hasp & staple 75mm – display packed	5013969901184	83024100	6
K21095	Traditional hasp & staple 95mm – boxed	5013969902594	83024100	6
K21095D	Traditional hasp & staple 95mm – display packed	5013969901191	83024100	6
K210115D	Traditional hasp & staple 115mm – display packed	5013969901177	83024100	6

<p>Technical product information</p>	<p>Materials – steel with chrome plating – staple is case hardened</p> <p>Security rating:</p> <table border="1" data-bbox="483 421 865 663"> <thead> <tr> <th>Item</th> <th>Security rating</th> </tr> </thead> <tbody> <tr> <td>K21075</td> <td>2</td> </tr> <tr> <td>K21075D</td> <td>2</td> </tr> <tr> <td>K21095</td> <td>4</td> </tr> <tr> <td>K21095D</td> <td>4</td> </tr> <tr> <td>K210115D</td> <td>5</td> </tr> </tbody> </table> <p>Staple Hole Dia:</p> <table border="1" data-bbox="483 770 865 1012"> <thead> <tr> <th>Item</th> <th>Staple Hole Dia</th> </tr> </thead> <tbody> <tr> <td>K21075</td> <td>9</td> </tr> <tr> <td>K21075D</td> <td>9</td> </tr> <tr> <td>K21095</td> <td>13.4</td> </tr> <tr> <td>K21095D</td> <td>13.4</td> </tr> <tr> <td>K210115D</td> <td>13.4</td> </tr> </tbody> </table> <p>Use environment- Light outdoor use</p> <p>Recommended applications- Cases, cupboards, lockers, toolboxes, sheds etc.</p>	Item	Security rating	K21075	2	K21075D	2	K21095	4	K21095D	4	K210115D	5	Item	Staple Hole Dia	K21075	9	K21075D	9	K21095	13.4	K21095D	13.4	K210115D	13.4
Item	Security rating																								
K21075	2																								
K21075D	2																								
K21095	4																								
K21095D	4																								
K210115D	5																								
Item	Staple Hole Dia																								
K21075	9																								
K21075D	9																								
K21095	13.4																								
K21095D	13.4																								
K210115D	13.4																								
<p>Standards compliance</p>	<p>None applicable</p>																								
<p>User health and safety information</p>	<p>None applicable</p>																								
<p>RoHS/WEEE compliance</p>	<p>These products do not fall within the scope of RoHS or WEEE regulations</p>																								
<p>Material safety data</p>	<p>None applicable</p>																								
<p>Warranty</p>	<p>KASP Hasp & staples are guaranteed against defects in manufacture and/or materials for 10 years Damage caused through inappropriate use or attempted break in is not covered</p>																								
<p>Country of origin</p>	<p>China</p>																								

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
K21075	28	75	25	66	55	122	35	77
K21075D	28	75	25	66	110	30	170	86
K21095	40	95	33	133	55	122	35	145
K21095D	40	95	33	133	110	32	170	155
K210115D	47	32	117	183	110	40	210	213

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
K21075	134	180	75	573		
K21075D	125	180	125	580		
K21095	134	180	75	983		
K21095D	147	185	125	1009		
K210115D	145	230	120	1366		

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
K21075	1	Bag	12	Box			113	Box
K21075D	15	Blister	5	Backing card			64	Box
K21095	1	Bag	12	Box			113	Box
K21095D	15	Blister	5	Backing card			79	Box
K210115D	23	Blister	7	Backing card			88	Box