

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5019512430](#)
Status: **Active**
Overview: [Easy-On FFC FPC Connectors](#)
Description: Easy-On FFC/FPC Connector, 0.50mm Pitch, V-Flip Series, Vertical, 4.05mm Height, 24 Circuits, Phosphor Bronze, Gold Plating

Documents:

3D Model	Datasheet (PDF)
Drawing (PDF)	Product Guide (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 5019510005-PS-000 (PDF)	Reference Guide (PDF)
Packaging Specification 5019519200-201 (PDF)	

General

Product Family	FFC/FPC Connectors
Series	501951
Overview	Easy-On FFC FPC Connectors
Product Name	Easy-On
Series Name	V-Flip
UPC	191128825597

Physical

Actuator Type	Front Flip
Circuits (Loaded)	24
Color - Resin	White
Contact Position	N/A
Durability (mating cycles max)	20
Mated Height	4.05mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer
Net Weight	284.400/mg
Number of Rows	1
Orientation	Vertical
PCB Locator	No
PCB Mounting	Surface Mount
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Plating min - Mating	0.102µm
Plating min - Termination	0.102µm
Polarized to PCB	No
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40° to +85°C
Wire/Cable Type	FFC/FPC


Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	50V

Material Info

Reference - Drawing Numbers

Packaging Specification	5019519200-201
Product Specification	5019510005-PS-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[501951 Series](#)

Mates With

Premo-Flex FFC Cable [15020](#)

This document was generated on 03/22/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION