



Sample photo

Order symbol: UL PC 150/100 LG
Product nbr: 6412316
Description: UL Enclosure, PC
Remarks: Grey cover

EAN: 6418074014399
El. number:
Finland:
Electric No. 8212030349
Denmark:
Electric No. Italy: 7351085U

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:				Rating:
Length	Width	Height		
mm:	180	130	100	
inch:	7.1	5.1	3.9	
Materials:				
Material:	Polycarbonate			
Base colour:	RAL 7035 -light grey			
Cover screws material:	Polyamide			
Cover colour:	RAL 7035 -light grey			
Cover screws colour:	Grey			
Gasket material:	TPE			
Temperatures:				
Temperature °C (short term):	-40 ... 120 °C			
Temperature °C (continuous):	-40 ... 80 °C			
Temperature °F (short term):	-40 ... 250 °F			
Temperature °F (continuous):	-40 ... 175 °F			

Rating:	
Ingress Protection (EN 60529): IP66/IP67	
Impact Resistance (EN 62262): IK08	
Electrical insulation: Totally insulated	
Halogen free (DIN/VDE 0472, Part 815): 1	
UV resistance: UL 508	
Flammability Rating: UL 746C 5"	
UL Type:	
Glow Wire Test (IEC 695-2-1) °C: 960	
Certificates:	
Underwriters Laboratories	
SGS Fimko	
UL Canada	
Gost R	

