



Sample photo

Order symbol: AR1086CHTSST
Product nbr: 8561058
Description: PC Enclosure
Remarks: Hinged transparent cover
w/S.S. Lockable twist latch

EAN: 6418074067128
El. number:
Finland:

Including: Hinged cover base with 10-32 brass inserts, latched cover with formed in place PUR gasket, and stainless hinge pin. Quick release latches. (Latch options available.) Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:			Accessories:		
	Length	Width	Height		
mm:	254	203	152	ALBP108 Aluminum Back Panel	
inch:	10.0	8.0	6.0	ADFP108 Dead Front Panel w/ screws	
				ASP108 Aluminum Swing Panel	
				ASPK108 Swing Panel Kit incl. Panel	
				ASPHK10 Swing Panel Kit w/o Panel	
				AMFL8 8" Mounting Flange Set	
Materials:				Rating:	
Material:	Polycarbonate			Ingress Protection (EN 60529): IP66/IP67	
Base colour:	RAL 7035 -light grey			Impact Resistance (EN 62262): IK09	
Cover screws material:	Stainless steel			Electrical insulation: Totally insulated	
Cover colour:	Clear transparent			Halogen free (DIN/VDE 0472, Part 815): 1	
Gasket material:	Polyurethane			UV resistance: UL 508	
				Flammability Rating: UL 508	
				Glow Wire Test (IEC 695-2-1) °C: 960	
				NEMA Class: NEMA 4, 4X, 6, 6P, 12, 13	
Temperatures:					
Temperature °C (short term):	-40 ... 140 °C				
Temperature °C (continuous):	-40 ... 80 °C				
Temperature °F (short term):	-40 ... 284 °F				
Temperature °F (continuous):	-40 ... 175 °F				
Accessories:					
ABP108	Painted Steel Back Panel				

