



Sample photo

Order symbol: UL PC 200/175 XHG
Product nbr: 6413329
Description: UL Enclosure, PC
Remarks: Grey cover

EAN: 6418074057075
EI. number:
Finland:
Electric No. Denmark: 8212030718
Electric No. Italy: 7351155U

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:			Rating:	
Length	Width	Height	Ingress Protection (EN 60529): IP66/IP67	
mm:	255	180	175	Impact Resistance (EN 62262): IK08
inch:	10.0	7.1	6.9	Electrical insulation: Totally insulated
Materials:			Halogen free (DIN/VDE 0472, Part 815): 1	
Material:	Polycarbonate		UV resistance: UL 508	
Base colour:	RAL 7035 -light grey		Flammability Rating: UL 746C 5"	
Cover screws material:	Polyamide		UL Type:	
Cover colour:	RAL 7035 -light grey		Glow Wire Test (IEC 695-2-1) °C: 960	
Cover screws colour:	Grey		Certificates:	
Gasket material:	Polyurethane		Underwriters Laboratories	
Temperatures:			SGS Fimko	
Temperature °C (short term):	-40 ... 120 °C		UL Canada	
Temperature °C (continuous):	-40 ... 80 °C		Gost R	
Temperature °F (short term):	-40 ... 250 °F			
Temperature °F (continuous):	-40 ... 175 °F			

