



Sample photo

Order symbol: UL PC F 65 T
Product nbr: 8714011
Description: UL Enclosure, PC
Remarks: Transparent cover

EAN: 6418074038920
El. number:
Finland:
Electric No. 8212031144
Denmark:
Electric No. Italy: 7202040U

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		230	80	65	Ingress Protection (EN 60529): IP66/IP67
inch:		9.1	3.1	2.6	Impact Resistance (EN 62262): IK08
					Electrical insulation: Totally insulated
Materials:					Halogen free (DIN/VDE 0472, Part 815): 1
Material:		Polycarbonate			UV resistance: UL 508
Base colour:		RAL 7035 -light grey			Flammability Rating: UL 746C 5"
Cover screws material:		Polyamide			UL Type:
Cover colour:		Clear transparent			Glow Wire Test (IEC 695-2-1) °C: 960
Cover screws colour:		Grey			
Gasket material:		Polyurethane			Certificates:
Temperatures:					Underwriters Laboratories
Temperature °C (short term):		-40 ... 120 °C			SGS Fimko
Temperature °C (continuous):		-40 ... 80 °C			UL Canada
Temperature °F (short term):		-40 ... 250 °F			Gost R
Temperature °F (continuous):		-40 ... 175 °F			

PICCOLO 230x80x65-85

