



Sample photo

Order symbol: UL PC 150/125 LG
Product nbr: 6412317
Description: UL Enclosure, PC
Remarks: Grey cover

EAN: 6418074057693
El. number:
Finland:
Electric No. 8212030381
Denmark:

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		180	130	125	Ingress Protection (EN 60529): IP66/IP67
inch:		7.1	5.1	4.9	Impact Resistance (EN 62262): IK08
					Electrical insulation: Totally insulated
Materials:					Halogen free (DIN/VDE 0472, Part 815): 1
Material:		Polycarbonate			UV resistance: UL 508
Base colour:		RAL 7035 -light grey			Flammability Rating: UL 746C 5"
Cover screws material:		Polyamide			UL Type:
Cover colour:		RAL 7035 -light grey			Glow Wire Test (IEC 695-2-1) °C: 960
Cover screws colour:		Grey			
Gasket material:		TPE			
Temperatures:					Certificates:
Temperature °C (short term):		-40 ... 120 °C			Underwriters Laboratories
Temperature °C (continuous):		-40 ... 80 °C			SGS Fimko
Temperature °F (short term):		-40 ... 250 °F			UL Canada
Temperature °F (continuous):		-40 ... 175 °F			Gost R

