

Product card: UL PC 200/88 XHG

[sales@fibox.com](mailto:sales@fibox.com)

Sample photo

**Including:** Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Product nbr: 6413330  
Description: UL Enclosure, PC  
Remarks: Grey cover  
Package: 4  
Unit: PCS  
Product group: MNX UL PC Enclosures  
EAN: 6418074057747  
Electric No. Denmark: 8212030776  
ETIM: EC000261 EC000261

**Support items:**

[Product card \(PDF\)](#)  
[Dimensional drawing \(mm\)](#)  
[Dimensional drawing \(inch\)](#)  
[Cad-files \(registration needed\)](#)

**Dimensions:**

Length (mm): 255.0  
Width (mm): 180.0  
Height (mm): 88.0

Length (inch): 10.0  
Width (inch): 7.1  
Height (inch): 3.5

**Installation position:**

Upright on a wall, pole or frame

**Materials:**

Material: Polycarbonate  
Base colour: RAL 7035 -light grey  
Cover screws material: Polyamide  
Cover colour: RAL 7035 -light grey  
Cover screws colour: Grey  
Gasket material: Polyurethane

**Temperatures:**

Temperature °C (short term): -40 ... 120 °C  
Temperature °C (continuous): -40 ... 80 °C  
Temperature °F (short term): -40 ... 250 °F  
Temperature °F (continuous): -40 ... 175 °F

**Ratings:**

Ingress Protection (EN 60529): IP66/IP67  
Impact Resistance (EN 62262): IK08  
Electrical insulation: Totally insulated  
Halogen free (DIN/VDE 0472, Part 815): 1  
UV resistance: UL 508  
Flammability Rating: UL 746C 5"  
UL Type:  
Glow Wire Test (IEC 695-2-1) °C: 960

**Certificates:**

Underwriters Laboratories  
[SGS Fimko](#)  
UL Canada  
[Gost R](#)

**Product is connected to following catalogs:**

Fibox Enclosures : UL ENCLOSURES : UL MNX PC