

**Order symbol:** AR865CHTSST  
**Product nbr:** 8561057  
**Description:** PC Enclosure  
**Remarks:** Hinged transparent cover  
w/S.S. Lockable twist latch

**EAN:** 6418074067104  
**El. number:**  
**Finland:**

Including: Hinged cover base with 10-32 brass inserts, latched cover with formed in place PUR gasket, and stainless hinge pin. Quick release latches. (Latch options available.) Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

| Dimensions:                  |                          |       |        | Accessories:                                |                             |
|------------------------------|--------------------------|-------|--------|---------------------------------------------|-----------------------------|
|                              | Length                   | Width | Height |                                             |                             |
| mm:                          | 203                      | 152   | 127    | ALBP86                                      | Aluminum Back Panel         |
| inch:                        | 8.0                      | 6.0   | 5.0    | ADFP86                                      | Dead Front Panel w/ screws  |
|                              |                          |       |        | ASP86                                       | Aluminum Swing Panel        |
|                              |                          |       |        | ASPK86                                      | Swing Panel Kit incl. Panel |
|                              |                          |       |        | ASPHK8                                      | Swing Panel Kit w/o Panel   |
|                              |                          |       |        | AMFL6                                       | 6" Mounting Flange Set      |
| Materials:                   |                          |       |        | Rating:                                     |                             |
| Material:                    | Polycarbonate            |       |        | Ingress Protection (EN 60529): IP66/IP67    |                             |
| Base colour:                 | RAL 7035 -light grey     |       |        | Impact Resistance (EN 62262): IK09          |                             |
| Cover screws material:       | Stainless steel          |       |        | Electrical insulation: Totally insulated    |                             |
| Cover colour:                | RAL 7035 -light grey     |       |        | Halogen free (DIN/VDE 0472, Part 815): 1    |                             |
| Gasket material:             | Polyurethane             |       |        | UV resistance: UL 508                       |                             |
| Temperatures:                |                          |       |        | Flammability Rating: UL 508                 |                             |
| Temperature °C (short term): | -40 ... 140 °C           |       |        | Glow Wire Test (IEC 695-2-1) °C: 960        |                             |
| Temperature °C (continuous): | -40 ... 80 °C            |       |        | NEMA Class: UL Type 4, 4X, 6, 6P, 12 and 13 |                             |
| Temperature °F (short term): | -40 ... 284 °F           |       |        |                                             |                             |
| Temperature °F (continuous): | -40 ... 175 °F           |       |        |                                             |                             |
| Accessories:                 |                          |       |        |                                             |                             |
| ABP86                        | Painted Steel Back Panel |       |        |                                             |                             |

