



Sample photo

Order symbol: UL PC B 85 T
Product nbr: 8714004
Description: UL Enclosure, PC
Remarks: Transparent cover

EAN: 6418074038821
El. number:
Finland:
Electric No. 8212031047
Denmark:
Electric No. Italy: 7202015U

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:				Rating:
	Length	Width	Height	
mm:	110	80	85	Ingress Protection (EN 60529): IP66/IP67
inch:	4.3	3.1	3.3	Impact Resistance (EN 62262): IK08
				Electrical insulation: Totally insulated
				Halogen free (DIN/VDE 0472, Part 815): 1
				UV resistance: UL 508
				Flammability Rating: UL 746C 5"
				UL Type:
				Glow Wire Test (IEC 695-2-1) °C: 960
Materials:				Certificates:
Material:	Polycarbonate			Underwriters Laboratories
Base colour:	RAL 7035 -light grey			SGS Fimko
Cover screws material:	Polyamide			UL Canada
Cover colour:	Clear transparent			Gost R
Cover screws colour:	Grey			
Gasket material:	Polyurethane			
Temperatures:				
Temperature °C (short term):	-40 ... 120 °C			
Temperature °C (continuous):	-40 ... 80 °C			
Temperature °F (short term):	-40 ... 250 °F			
Temperature °F (continuous):	-40 ... 175 °F			

PICCOLO 110x80x65-85

