

UL MNX UL PC 100/35 LG



Sample photo

Order symbol:	UL PC 100/35 LG
Product nbr:	6412301
Description:	UL Enclosure, PC
Remarks:	Grey cover

EAN: 6418074014221
El. number:
 Finland:
 Electric No. 8212030064
 Denmark:
 Electric No. Italy: 7351010U

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:	Length	Width	Height	Rating:
mm:	130	80	35	Ingress Protection (EN 60529): IP66/IP67
inch:	5.1	3.1	1.4	Impact Resistance (EN 62262): IK08
Materials:				Electrical insulation: Totally insulated
Material:	Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): 1
Base colour:	RAL 7035 -light grey			UV resistance: UL 508
Cover screws material:	Polyamide			Flammability Rating: UL 746C 5"
Cover colour:	RAL 7035 -light grey			UL Type:
Cover screws colour:	Grey			Glow Wire Test (IEC 695-2-1) °C: 960
Gasket material:	TPE			Certificates:
Temperatures:				Underwriters Laboratories
Temperature °C (short term):	-40 ... 120 °C			SGS Fimko
Temperature °C (continuous):	-40 ... 80 °C			UL Canada
Temperature °F (short term):	-40 ... 250 °F			Gost R
Temperature °F (continuous):	-40 ... 175 °F			

