

Simple and easy-to-use vacuum cleaner - for general everyday cleaning

VP100 offers you simple cleaning solution. Intuitive design with simple operation ensures that VP100 can be used with very little instruction. VP100 is fully compatible with the range of accessories offered with the rest of the Nilfisk dry canister vac portfolio. It allows to be more flexible in replacement of accessories and reduce the overall operating costs of your complete Nilfisk cleaning solution





To ensure its ease of use, it has standard features such as:

- Intuitive on/off switch
- Compact cable storage
- Accessory storage
- Simple dust bag replacement




Picture shown may not represent model quoted

• Standard equipment

Included accessories	Ref. no.	Min. required	VP100-EU DRY VACUUM CLEANER	VP100-UK DRY VACUUM CLEANER	VP100-CN DRY VACUUM CLEANER
Hose and Connection					
 HOSE CPL D32	147 0765 500	1	•	•	•
Combination Nozzle					
 COMBI NOZZLE RD277 KIT	107411677	1	•	•	•
Nozzle - Vacuum					
 BRUSH NOZZLE D32	140 8244 500	1	•	•	•
 CREVICE NOZZLE D32 L153 BLACK	147 0146 500	1	•	•	•
Filter					
DSU8 AND DSU10 MAIN FILTER ASSEMBLY KIT	VA81235	1	•	•	•
EAGLE2 MOTR FRONT FILTER PLATE KIT	VA85064	1	•	•	•
Extension Tube					



Simple and easy-to-use vacuum cleaner - for general everyday cleaning

Included accessories	Ref. no.	Min. required	VP100-EU DRY VACUUM CLEANER	VP100-UK DRY VACUUM CLEANER	VP100-CN DRY VACUUM CLEANER
 EXTENSION TUBE STEEL D32	140 8246 040	1	•	•	•



Model	VP100-EU DRY VACUUM CLEANER	VP100-UK DRY VACUUM CLEANER	VP100-CN DRY VACUUM CLEANER
Ref. no.	50000470	50000471	50000472

PRODUCT FEATURES

Dust bag 1 pcs.	•	•	•
Storage of accessories	•	•	•
Cable storage	•	•	•






Technical specifications	VP100-EU DRY VACUUM CLEANER	VP100-UK DRY VACUUM CLEANER	VP100-CN DRY VACUUM CLEANER
Voltage (V)	220-240	220-240	220
Frequency (Hz)	50-60	50-60	50
IP protection class	IP20	IP20	IP20
Rated power (W)	880	880	1000
Suction power end of tube (W)	192	192	205
Airflow (l/sec.)	30	30	32
Sound pressure level dB(A) IEC/EN 60335-2-69	62.5	62.5	
Cable length (m)	8	8	8
Dust bag capacity (l)	10	10	10
Main filter area (cm ²)	1100	1100	1100
Number of filters	4	4	4
Length x width x height (mm)	340x320x340	340x320x340	340x320x340
Weight (kg)	5.2	5.2	5.2

• Standard equipment, ○ Supplementary accessories, □ Mountable equipment

Accessories	Ref. no.	Min. required	VP100-EU DRY VACUUM CLEANER	VP100-UK DRY VACUUM CLEANER	VP100-CN DRY VACUUM CLEANER
Nozzle - Vacuum					
 BRUSH NOZZLE D32	140 8244 500	1	•	•	•
 CREVICE NOZZLE D32 L153 BLACK	147 0146 500	1	•	•	•



Simple and easy-to-use vacuum cleaner - for general everyday cleaning

Accessories		Ref. no.	Min. required	VP100-EU DRY VACUUM CLEANER	VP100-UK DRY VACUUM CLEANER	VP100-CN DRY VACUUM CLEANER
Extension Tube						
	EXTENSION TUBE STEEL D32	140 8246 040	1	•	•	•
Dust Bag and Filter						
	DUST BAG PAPER 10-PCS	140 8618 000	1	○	○	○
Hose and Connection						
	HOSE CPL D32	147 0765 500	1	•	•	•
Filter						
	DSU8 AND DSU10 MAIN FILTER ASSEMBLY KIT	VA81235	1	•	•	•
	EAGLE2 MOTR FRONT FILTER PLATE KIT	VA85064	1	•	•	•
Other						
	HEPA FILTER H13	VA85065	1	○	○	○
	VP100 PACKING CLIP	VA81570	1	○	○	○
Combination Nozzle						
	COMBI NOZZLE RD277 KIT	107411677	1	•	•	○