

## 4-Port Desktop KVM Switch (USB)

MODEL NUMBER: **B006-VU4-R**



### Description

Tripp Lite's 4-port Desktop USB KVM Switch is the optimal solution for controlling up to 4 USB computers from one VGA monitor and USB keyboard/mouse. Manually switch between connected computers using pushbuttons or hotkey controls; or, monitor connected computers automatically via Auto Scan Mode. The B006-VU4-R is operating system independent, and works with all computers that have an available VGA and USB port. It supports video resolutions up to 2048 x 1536, and features a compact design that does not require software or complicated set-up procedures. Constructed of heavy-duty steel housing. Order P758 Cables separately.

### Features

- Control up to 4 USB computers from a single VGA monitor and USB keyboard/mouse
- Order P758 Cables separately
- Port LEDs illuminate Dim Orange to indicate a computer is connected, and Bright Orange to indicate it is the selected port
- Supports video resolutions up to 2048 x 1536, DDC2B
- No software or complicated set-up procedures required
- Manually switch between connected computers via front panel pushbuttons or hotkey commands
- Automatically monitor connected computers via Auto Scan Mode
- Compatible with all major operating systems
- Compatible with most mice; including scroll mice
- Constructed of heavy-duty steel housing

## Specifications

### OVERVIEW

### Highlights

- Control up to 4 USB computers from a single VGA monitor and USB keyboard/mouse
- Switch between connected computers via pushbuttons or hotkey commands
- Auto Scan Mode allows monitoring of connected computers without manually switching between them
- Compatible with all major operating systems
- Supports video resolutions up to 2048 x 1536, DDC2B

### Package Includes

- B006-VU4-R 4-port USB KVM Switch
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A / Output: 5.3V, 2.4A )
- Owner's manual



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

UPC Code	037332152947
Console	No
Max CPU	4
Technology	USB; VGA/SVGA
<b>VIDEO</b>	
Max Supported Video Resolution	2048 X 1536, DDC2B
<b>INPUT</b>	
External Power Supply Plug(s)	NEMA 1-15P North America
<b>POWER</b>	
External Power Supply Input Specs (V / Hz / A)	100-240V/ 50/60Hz/ 0.5A
External Power Supply Output Specs (V / A)	5.3V/ 2.4A
External Power Supply Cord Length (ft.)	5
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	Online Selected (Orange)
<b>PHYSICAL</b>	
LCD Monitor (cm)	Not Applicable
Shipping Dimensions (hwd / cm)	8.89 x 24.89 x 22.10
Shipping Dimensions (hwd / in.)	3.50 x 9.80 x 8.70
Shipping Weight (kg)	1.00
Shipping Weight (lbs.)	2.20
Unit Dimensions (hwd / cm)	4.32 x 20.07 x 7.37
Unit Dimensions (hwd / in.)	1.7 x 7.9 x 2.9
Unit Weight (kg)	0.68
Unit Weight (lbs.)	1.50
<b>ENVIRONMENTAL</b>	
BTUs	7.1694 BTU/Hr
<b>COMMUNICATIONS</b>	
Port Control	Push Buttons, Hotkeys
IP Remote Access	No



<b>CONNECTIONS</b>	
Ports	4
PC/Server Connections	USB; VGA
Side A - Connector 1	(4) HD15 (MALE)
Side A - Connector 2	(4) USB B (FEMALE)
Side B - Connector 1	(1) HD15 (FEMALE)
Side B - Connector 2	(2) USB A (FEMALE)
Computer Keyboard and Mouse Interface	USB
Computer Monitor Interface	VGA
Console Keyboard and Mouse Interface	USB
Console Monitor Interface	VGA
<b>FEATURES &amp; SPECIFICATIONS</b>	
Autoscan (Y,N)	Y
Autoscan Duration	11 TO 99 SECONDS; USER-DEFINEABLE
Number of Users	1
NIAP-Certified Secure	No
USB Specification	USB 2.0 (up to 480 Mbps)
Cat5 KVM Switch	No
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>