

# **CLIFF**

## S1C JACK SOCKETS

#### FCR1117 - S1C/S/BBB x2 Special Nose







2 HOLES 11.4±0.1


OVER


2 HOLES

Ø9.05 +0.2 / -0

SPECIAL NOSE

THREAD





PLUG IS WITHDRAWN.

Specification:


Withstand voltage: 2000V DC minimum

Maximum current: 5 amp

-10° C to + 70° C Temperature rating:

< 100mΩ Life: 10,000+ operations. Nominal contact resistance: < 50mΩ

#### FCR1124W - S1C/SH/BBB x2 with Earth washer and nuts.



Specification:

© CLIFE 03/2021 ISS 1

Withstand voltage: 2000V DC minimum


Maximum current: 5 amp

-10° C to + 70° C Temperature rating:

Life: 10,000+ operations. < 100mΩ

Nominal contact resistance: < 50mΩ

19.05 ±0.1 2 HOLES Ø11.4±0.1 SWITCH CONTACTS OPEN WHEN PANEL CUTOUT DETAIL PLUG IS INSERTED, CLOSE WHEN PLUG IS WITHDRAWN.



For further information, contact sales@cliffuk.co.uk

### **Cliff Electronic Components Limited**,

76 Holmethorpe Avenue, Holmethorpe Ind. Estate, Redhill, Surrey RH1 2PF U.K.

Tel: +44 (0)1737 771375 Fax: +44 (0)1737 766012





www.cliffuk.co.uk