



List No. NHXB32

NH / NM / NMX

32A SP Type B 6kA MCB



- Single pole MCB, 32A B curve
- Energy limiting Class 3
- Balcony terminal position

Product Specification Data

Release characteristic	B
Number of poles (total)	1
Number of protected poles	1
Rated current	32 A
Rated voltage	230 V
Rated insulation voltage U_i	400 V
Rated impulse withstand voltage U_{imp}	4 kV
Rated short-circuit breaking capacity I_{cn} EN 60898 at 230 V	6 kA
Rated short-circuit breaking capacity I_{cn} EN 60898 at 400 V	6 kA
Voltage type	AC
Frequency	50 Hz
Current limiting class	3
Suitable for flush-mounted installation	No
Concurrently switching N-neutral	No
Over voltage category	3
Additional equipment possible	No
Width in number of modular spacings	1
Built-in depth	73 mm
Degree of protection (IP)	IP20
Ambient temperature during operating	-5 - +40 °C
Connectable conductor cross section multi-wired	.75-25 mm ²
Product Standard/s	BS EN 60898-1
CE Mark	Yes
WEEE Symbol	Yes