

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2163031224](#)  
**Status:** **Active**  
**Overview:** [Off-the-Shelf Pre-Crimped Leads](#)  
**Description:** Pre-Crimped Lead MX150-Male-to-Pigtail, Gold (Au) Plating, 300.00mm Length, 14 AWG, Black

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Datasheet \(PDF\)](#)

**General**

Product Family	Cable Assemblies
Series	<a href="#">216303</a>
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	MX150 Terminal-to-Pigtail
Overview	<a href="#">Off-the-Shelf Pre-Crimped Leads</a>
Product Name	MX150
UPC	195842071445

**Physical**

Cable Length	300.00mm
Circuits (Loaded)	1
Color - Resin	Black
Gender	Male-Pigtail
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Net Weight	10.583/g
Packaging Type	Bag
Single Ended	Yes
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.70mm max.
Wire Size AWG	14
Wire/Cable Type	TXL

**Electrical**

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	14V DC

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing	2163031221-000
---------------	----------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)9139-DC (19  
Jan 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[216303 Series](#)

**Use With**

MX150 Dual Row Housing [33482](#) . MX150  
Single Row Housing [33481](#) . MX150 Hybrid  
Housing [33486](#)