

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2163031204](#)
Status: **Active**
Overview: Off-the-Shelf Pre-Crimped Leads
Description: Pre-Crimped Lead MX150-Male-to-Pigtail, Gold (Au) Plating, 300.00mm Length, 18 AWG, Black

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General

Product Family Cable Assemblies
Series [216303](#)
Application Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration Pre-crimped Lead Only
Connector to Connector MX150 Terminal-to-Pigtail
Overview Off-the-Shelf Pre-Crimped Leads
Product Name MX150
UPC 195842071346

Physical

Cable Length 300.00mm
Circuits (Loaded) 1
Color - Resin Black
Gender Male-Pigtail
Material - Metal High Performance Alloy (HPA)
Material - Plating Mating Gold
Net Weight 3.949/g
Packaging Type Bag
Single Ended Yes
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 2.70mm max.
Wire Size AWG 18
Wire/Cable Type TXL

Electrical

Current - Maximum per Contact Contact Molex
Voltage - Maximum 14V DC

Material Info

Reference - Drawing Numbers

Sales Drawing 2163031201-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[216303](#) Series

Use With

MX150 Dual Row Housing [33482](#) . MX150
Single Row Housing [33481](#) . MX150 Hybrid
Housing [33486](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION