

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2163011102](#)
Status: **Active**
Overview: [Off-the-Shelf Pre-Crimped Leads](#)
Description: Pre-Crimped Lead MX150 Female-to-Pigtail, Tin (Sn) Plating, 150.00mm Length, 18 AWG, Black

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	216301
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	MX150 Terminal-to-Pigtail
Overview	Off-the-Shelf Pre-Crimped Leads
Product Name	MX150
UPC	195842070622

Physical

Cable Length	150.00mm
Circuits (Loaded)	1
Color - Resin	Black
Gender	Female-Pigtail
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Tin
Net Weight	2.263/g
Packaging Type	Bag
Single Ended	Yes
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.70mm max.
Wire Size AWG	18
Wire/Cable Type	TXL

Electrical

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	14V DC

Material Info

Reference - Drawing Numbers

Sales Drawing	2163011101-000
---------------	----------------



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[216301](#) Series

Use With

MX150 Dual Row Housing [33472](#) . MX150
Single Row Housing [33471](#) . MX150 Hybrid
Housing [33476](#)