

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2174701125](#)
Status: **Active**
Overview: [Off-the-Shelf Pre-Crimped Leads](#)
Description: Pre-Crimped Lead Ultra-Fit Female-to-Ultra-Fit Female, Tin (Sn) Plating, 450.00mm Length, 16 AWG, Black

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General

Product Family Cable Assemblies
Series [217470](#)
Application Power, Wire-to-Board
Assembly Configuration Pre-crimped Lead Only
Connector to Connector Ultra-Fit Crimp Terminals
Overview [Off-the-Shelf Pre-Crimped Leads](#)
Product Name Ultra-Fit
UPC 195842069541

Physical

Cable Length 450.00mm
Circuits (Loaded) 1
Color - Resin Black
Gender Female-Female
Material - Metal High Conductivity Copper
Material - Plating Mating Tin
Net Weight 7.103/g
Packaging Type Bag
Single Ended No
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 2.03-2.39mm
Wire Size AWG 16
Wire/Cable Type UL 1061

Electrical

Current - Maximum per Contact 12.0A
Voltage - Maximum 600V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Sales Drawing 2174701121-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[217470 Series](#)

Use With

Ultra-Fit Tangless Receptacle
Housing Link:[172256](#), [172258](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION