



- » [HOME](#)
- » [OVERVIEW](#)
- » [PRODUCTS](#)
- » [NEWS](#)
- » [WHERE TO BUY](#)
- » [CONTACT US](#)
- » [SUPPORT](#)



Lastest Products

PWI-AC90CBV2

90Watt Universal switching-mode power adapter for notebooks and LCDs



PWI-USB-HDV

Multi-Display USB 2.0 to DVI/VGA/HDMI adapter (up to 6 displays*)



PWI-DP-HDMI

Connect HDMI interface to a Display port interface



PWI-DP-VGA

[SHOW LARGE PICTURE](#)



PRODUCT FEATURES

Allows you to connect any monitor or projector with a VGA interface to a laptop or desktop with a Display port interface, without the need for a Display port embedded terminal device.

PRODUCT SPECIFICATION

Input: DisplayPort Male, Output: VGA Female.

Chipset: ANX9832.

DisplayPort Interoperability specification V1.1a compliant receiver offering 1.62 and 2.7Gbps over 4 lanes.

Max Resolution: 1920 x1200 1080P @60Hz. Video Amplifier Bandwidth at 162 MHz.

ESD protect Mode: Human Body /8 kV, Machine/400V, and Charged Device/2 kV.

EDID pass-through from PC source to display; Spread Spectrum for EMI reduction.

PC Support: VGA, SVGA, XGA, SXGA, UXGA, WUXGA.

HDTV Support: 480i, 576i, 480p, 576p, 1080i and 1080p.

Low power operation-Active@400mW, standby@33mW. Power from Displayport.

UL 20276 32AWG, OD5. 5mm, Jacket PVC Black. Nickel Plated, Length: 20cm (7.9?).

RoHS, FCC & CE compliant.



PWI-DP-DVI



PWI-DP-HDMI

