



INTERNATIONAL HARDWARE SHOW PRODUCT BRIEFING

March 1th - March 4th

XP18R



An Ultra-Bright Large-Format Torch in COAST's NEW Durable "Extreme Performance" Line of Portable Lighting Solutions

The COAST XP18R torch delivers a whopping 3500 lumens in Turbo Mode, with 1000 lumens on High, in COAST's crisp, consistent beam. Turbo mode can be accessed with a long push of the rear switch, along with three other modes (low, medium, and high).

The torch is able to achieve such incredible specs due to its COAST ZITHION-X[™] rechargeable battery, which can be charged in the torch via a Pro-Tek port or outside of the torch. The torch features COAST's Dual Power[™] technology, meaning the torch is compatible with six AA alkaline batteries (sold separately).

This powerhouse — the most powerful in COAST's new XP (Extreme Performance) line of torches — features a real-time power indicator plus patented slide-focusing optical technology that shines clean flood light and piercing spot light with seamless transitions between.

- 3500 lumens on Turbo Mode, and 1000 lumens on High
- Length: 10 in. / 25.5 cm
- ZITHION-X[™] rechargeable battery (included), or 6 x AA batteries (sold separately)






XP18R PURE BEAM FOCUSING TORCH



DUAL POWER

ZITHION-X™Rechargeable — Also works with Alkaline batteries















XP11R



This Workhorse Torch Brings 2000 Lumens on Turbo Mode in COAST's NEW Durable "Extreme Performance" Line of Portable Lighting Solutions

The XP11R brings a new mode to COAST handhelds — Turbo Mode — which will provide 2000 lumens featuring COAST's famously consistent beam. Turbo mode can be accessed with a long push of the rear switch, along with three other modes (low, medium, and high).

The COAST XP11R torch delivers brightest-in-class light, multi-beam capability powered by a COAST ZITHION-X[™] rechargeable battery, which can be charged in the torch via a Pro-Tek port or outside of the torch. The torch also features COAST's Dual Power[™] technology, meaning it's also compatible with three AAA alkaline batteries (sold separately).

This workhorse features a real-time power indicator plus patented slide-focusing optical technology that shines clean flood light and piercing spot light with seamless transitions between.

- 2000 lumens on Turbo Mode, and 1000 lumens on High
- Length: 6.02 in. / 15.30 cm
- ZITHION-X[™] rechargeable battery (included), or 3 x AAA batteries (sold separately)





XP11R PURE BEAM FOCUSING TORCH



DUAL POWER


ZITHION-X™Rechargeable — Also works with Alkaline batteries















XP9R



A Powerful Mid-Sized Torch in COAST's NEW Durable "Extreme Performance" Line of Portable Lighting Solutions

COAST brings 1000 lumens to a compact, 5.25-inch torch in its new XP9R. The COAST XP9R Dual Power[™] torch delivers brightest-in-class light featuring COAST's famously consistent beam. The torch features three light output modes and with a slide focus, and delivers multi-beam capability.

The torch can deliver this powerful brightness courtesy of COAST's patented ZITHION-X[™] rechargeable battery. The XP9R is also compatible with two CR123s disposable lithium batteries (sold separately).

This all-purpose handheld torch features patented slide-focusing optical technology that shines clean flood light and piercing spot light with seamless transitions between.

- 1000 lumens with rechargeable cell
- Length: 5.25 in. / 13.28 cm
- ZITHION-X[™] rechargeable battery (included), or 2 x CR123 batteries (sold separately)





XP9R PURE BEAM FOCUSING TORCH



DUAL POWER


ZITHION-X™Rechargeable — Also works with CR123 Lithium batteries















XP6R



An Ultra-Compact Pocket Flashlight in COAST's NEW Durable "Extreme Performance" Line of Portable Lighting Solutions

Big on light, small on size. The COAST XP6R torch delivers brightest-in-class light with a new, more rugged look consistent with COAST's new line of XP (Extreme Performance) torches. The XP6R is 3.5 inches in length and packs a punch, with 400 lumens of maximum brightness. The torch features three light output levels, and multi-beam capability powered by a COAST ZITHION-XTM rechargeable battery.

This torch is equipped with COAST's Dual Power[™] technology, meaning the torch is also compatible with a CR123 disposable lithium battery (sold separately).

This pocket-sized handheld torch features patented slide-focusing optical technology that shines clean flood light and piercing spot light with seamless transitions between.

- 400 lumens with rechargeable battery cell
- Length: 3.55 in. / 9.04 cm
- ZITHION-X[™] rechargeable battery (included), or a CR123 battery (sold separately)





XP6R PURE BEAM FOCUSING TORCH



DUAL POWER


ZITHION-X™Rechargeable — Also works with a CR123 Lithium battery















XPH34R



COAST Introduces its Most Powerful Ever 2000 Lumens Head torch in COAST's NEW Durable "Extreme Performance" Line of Portable Lighting Solutions

The COAST XPH34R rechargeable head torch gives users amazing versatility and delivers COAST's most powerful brightness. The torch has a maximum lumen output of 2000 on Turbo Mode, and 1000 lumens on High.

The XPH34R features a compact, dust-resistant aluminum body that rolls in its bracket for dynamic directional lighting. You can pull the torch out of the bracket to use as a handheld; there is also a magnet on the battery cap which allows you to affix the torch to metal surfaces.

Powered by a COAST ZITHION-X[™] rechargeable battery with a real-time battery life indicator, the torch features a twist focus, and four light output options. The light features COAST's Dual Power[™] technology, meaning the torch is also compatible with two CR123 batteries (sold separately) or three AAA alkaline batteries (sold separately).

- 2000 lumens on Turbo Mode with rechargeable battery cell
- ZITHION-X[™] rechargeable battery (included), 2 x CR123 (sold separately), or 3 x AAA batteries (sold separately)






XPH34R MULTI-PURPOSE HEAD TORCH



ZITHION-X™Rechargeable — Also works with CR123 Lithium or Alkaline batteries













XPH30R



A Rechargeable Head torch that Delivers 1000 Lumens in COAST's NEW Durable "Extreme Performance" Line of Portable Lighting Solutions

The COAST XPH30R head torch gives users amazing versatility and powerful brightness. The torch has a maximum lumen output of 1000 on Turbo Mode, and 700 lumens on High.

The XPH30R features a compact, dust-resistant aluminum body that rolls in its bracket for dynamic directional lighting. You can pull the torch out of the bracket to use as a handheld; there is also a magnet on the battery cap which allows you to affix the torch to metal surfaces.

Powered by a COAST ZITHION-X[™] rechargeable battery with a real-time battery life indicator, the torch features a twist focus, and four light output options. The torch features COAST's Dual Power[™] technology, meaning the torch is also compatible with two CR123 disposable lithium batteries (sold separately).

- 1000 lumens on Turbo Mode with rechargeable battery cell
- COAST ZITHION-X[™] rechargeable battery (included), or 2 x CR123 batteries (sold separately)






XPH30R MULTI-PURPOSE HEAD TORCH



DUAL POWER


ZITHION-X™Rechargeable — Also works with CR123 Lithium batteries













TRUSTED TOUGH.™



XPH25R



A Compact Rechargeable Head torch in COAST's NEW Durable "Extreme Performance" Line of Portable Lighting Solutions

The COAST XPH25R headlamp gives users amazing versatility. The torch features a compact, dust-resistant aluminum body that rolls in its bracket for dynamic directional lighting.

You can pull the torch out of the bracket to use as a handheld; there is also a magnet on the battery cap which allows you to affix the torch to metal surfaces.

Powered by a COAST ZITHION-X[™] rechargeable battery with a real-time battery life indicator, the torch features a twist focus, and three light output options.

The torch features COAST's Dual Power[™] technology, meaning the torch is also compatible with a CR123 disposable lithium battery (sold separately).

- 400 lumens on high with rechargeable battery cell
- ZITHION-X[™] rechargeable battery (included), or a CR123 batteries (sold separately)





XPH25R MULTI-PURPOSE HEAD TORCH



DUAL POWER


ZITHION-X™Rechargeable — Also works with a CR123 Lithium battery













TRUSTED TOUGH.™



FL1R

Micro Rechargeable Head Torch

The FL1R is COAST's new rechargeable micro head torch. At just 1.41 ounces, the FL1R is made for activities where size and weight are important — like running or backpacking.

The FL1R has an embedded rechargeable battery, reducing the weight considerably, and will run for 1.5 hours on high.

The head torch also has a lockout feature to avoid having it turn on in a pack – hold the button for 5 seconds and it will be locked off.

The light is weather proof, and comes with a clip for attaching to sternum straps or hats, and a headband for regular headlamp fit. 2 white light modes and one red light mode.

• 300 lumens

• Runtime (High): 1h 30min; Runtime (Low): 4h

Weight: 1.4 oz. / 40 g


Embedded Li-Ion Cell





MICRO HEAD TORCH

















HX4

The Handy Clip Torch from COAST

The HX4 chip-on-board (C.O.B.) clip torch is the ideal dual color everyday carry torch. By combining red and white LEDs, the HX4 LED clip torch is excellent when you need bright illumination or need to use it in situations where you need to preserve your night vision.

The universal clip on the torch makes it easy to clip on pockets or even the bill of your hat, while the integrated magnets allow the HX4 to be placed on magnetic surfaces. Once placed or clipped to a surface, the torch features a 180-degree beam adjustment and enable the optimal beam placement for the user.

- 80 lumens
- Weight: 1.8 oz / 53 g; Runtime: 3 hour and 45 minute
- 2 x AAA batteries





HX4 DUAL COLOR C.O.B. CLIP TORCH















PS400S

New Polysteel Torch – Now Has a Powerful Magnet in the Handle and a Swivel Head

COAST took its middle-size Polysteel handheld torch, the PS400, and gave it new features: a magnet in the handle and a swiveling head. The head of the torch turns 180 degrees at the bevel, giving people the ability to be flexible on where the torch is pointing.

The PS400S Torch is waterproof, drop proof, and crush proof while possessing our Pure Beam Optics System with twist focus to make the torch ultra-durable and ready to weather any storm.


With a stainless-steel core and a poly outer material, we put this torch to the test, and it passed each one with style. With Coast's commitment to quality, the PS400S Torch is impact resistant, waterproof, and its LED is virtually unbreakable.

- 440 lumens
- Runtime (High): 4h; Runtime (Low): 27h
- Length: 5.75 in / 14.6 cm / Weight: 6.4 oz. / 181 g
- 4 x AAA batteries





PS400S POLYSTEEL TORCH















PS700 C.O.B.

New Polysteel Torch – Now Has a Powerful Magnet in the Handle and is Rechargeable With Two C.O.B. Torches

COAST continues to innovate with its Polysteel line with its new Polysteel 700R, which is both rechargeable and features two chip-on-board lights in the handle, to make it both a handled torch and an work torch.

The PS700R is waterproof, drop proof, and crush proof while possessing COAST's patented Pure Beam Optics System with twist focus to make the torch ultra durable and ready to weather any storm.

The torch runs on either four AA alkaline batteries (included) or ZITHION™ rechargeable battery (sold separately)

With a stainless steel core and a poly outer, the PS700R Torch is impact resistant, waterproof, and its LED is virtually unbreakable.

- 800 lumens on high
- Runtime (Low): 45h
- Length: 8.3 in / 21 cm / Weight: 12.6 oz. / 360 g
- 4 x AA batteries (included) or ZITHION™ rechargeable battery (sold separately)





PS700 C.O.B. POLYSTEEL WORK TORCH



DUAL POWER

Alkaline Powered — Also works with COAST's ZITHION™ Rechargeable battery















PS100

A NEW Waterproof, Durable Pen Torch

The COAST PS100 pen torch combines Polysteel strength with pocket-sized convenience to create a go-anywhere, waterproof lighting solution.

This drop proof and dust proof torch features COAST's Bulls-Eye Spot Beam, which casts a bright hot spot on the object, surrounded by a soft halo of transitional light to increase the total field of view. From spotting animals in the woods to identifying suspects, this beam cuts through darkness.


This torch is perfect for everyday use in the field with a one-handed switch, and a steel pocket clip for storage.

- 100 lumens
- Length: 6 in. / 15.3 cm
- 2 x AAA batteries





PS100 POLYSTEEL POCKET PEN TORCH













PS20

A New Polysteel Inspection Beam Pen Torch

COAST took its most popular pen torch and made it waterproof, drop proof, and crush proof — the PS20 is the Polysteel version of COAST's G20 inspection pen torch.

The PS20 is a versatile, reliable, and extremely tough for everyday use. Whether you store it in your shirt pocket, pants pockets, or tool bag, the PS20 with its Inspection Beam Optic is a torch for everyday use that you should keep close. Optimized for up-close use with crisp edges and little glare, the perfectly circular beam illuminates where and when you need it.

The PS20 torch is backed by COAST's five year warranty against defects in materials and workmanship. Tested and rated to ANSI/FL1 standards.

Runtime (High): 12hr

Length: 6 in. / 15.3 cm; Weight: 1.98 oz. / 56 g

2 x AAA batteries





PS20 POLYSTEEL PEN TORCH













PM300

Pro-Mount Pivot Torch

This innovative new area torch from COAST brings unprecedented versatility to a powerful portable LED torch.

The torch is compact and folds flat with a "handle" that rotates around the torch's body 360 degrees, which can act either as a handle to carry the torch or a prop to set down and point the torch where you need it.

It also has a strong rare-earth magnet on the handle to affix the torch to metal surfaces.

The torch has three light levels, and features COAST's patented Long Distance Focusing Optic with a twist

flood-to-spot beam focus.

• 700 lumens on high

 Runtime (High): 11h; Runtime (Low): 60h

 Length: 7in / 17.7 cm / Weight: 17.6 oz. / 500 g

6 x AA batteries





PM300 PRO-MOUNT PIVOT TORCH















PM650R

Pro-Mount Rotating Torch

The PM650R is new versatile rechargeable area torch at an entry-level price point.

It has a magnetic base that can affix firmly to any metal surface with a rubber pad to conform to uneven surfaces.

The 700-lumen torch has three light levels, the bezel rotates 180 degrees, and focuses to illuminate both broad or narrow areas.

The PM650R is rechargeable, with an embedded Li-ion battery. The torch will run continuously on AC/DC power using the included power cord with the micro USB charging port.


- 700 lumens on high
- Runtime (High): 4h; Runtime (Low): 19h
- Length: 4 in / 10.1 cm / Weight: 11.2 oz. / 320 g
- Embedded Li-Ion Cell





PM650R PRO-MOUNT ROTATING TORCH





MAGNETIC BASE CURVED SURFACE COMPATIBILITY













WLR1

COAST Brings Portability to Work Torches With a New Rechargeable, Compact Work Torch

The WLR1 is a compact LED work torch that runs off both AC power and a rechargeable Embedded Li-ion Cell. This gives contractors flexibility and portability in their work torch, should they find themselves without power.

The powerful, compact floodlight packs a punch at 1150 lumens and can rotate 180 degrees.

The torch also features a USB out port to charge electronics from the torch whether plugged in or running off the Li-ion cell.





WLR1 FOCUSING WORK TORCH





















EAL13



COAST's New Versatile, Tough, and Compact Emergency Area Torch

The EAL13 is the compact, feature-rich portable torch that is made for emergency situations both at home or on the go. The torch has a 330-lumen output on high and will run for 120 hours on low.

The EAL13 is rated IP54 storm proof and built for any situation, with a tough, drop-proof nylon body and polycarbonate dome and globe construction.

Users can remove the globe to allow for higher lumen output — and with carabiners on the top and bottom, the lantern can be hung to provide overhead lighting.

The EAL13 features magnets on the underside of the lantern to affix to metal surfaces, as well.

- Runtime (Low) 330 lumens with a 120-hour runtime on low
- Features a magnetic bottom to affix to metal surfaces
- 3 x AA batteries (sold separately)



COA57

EAL13 5-IN-1 EMERGENCY AREA TORCH















EAL22



COAST's New Versatile, Storm Proof Emergency Area Torch

The EAL22 is COAST's new emergency area torch with a bevy of features made for any situation where portable lighting is needed. The torch is incredibly bright on high, 1300 lumens, with the ability to run for 40 hours on the lowest brightness setting.

The EAL22 is rated IP54 storm proof with a tough, drop-proof nylon body, polycarbonate dome and globe construction.

Users can also remove the globe to allow for higher lumen output, and with carabiners on the top and bottom, the lantern can be hung to provide overhead lighting with ease.

The USB charging port also allows users to charge phones or accessories in emergency situations from the three (3) D-cell batteries, and a battery indicator on the switch allows users to anticipate remaining battery life.

- 1300 lumens with a 40-hour runtime on low
- Has a USB cell-phone charging port with a waterproof cover
- 3 x D cell batteries (sold separately)





EAL22 5-IN-1 EMERGENCY AREA TORCH











INTEGRATED Carabiner

FOLDABLE HANDLE



TOUGH POLY CASING





SMART POWER SWITCH + BATTERY LIFE INDICATOR

INTEGRATED Carabiner













EAL22R



COAST Is Launching The Best Rechargeable Emergency Area Torch On The Market

The EAL22R is an all-new rechargeable, feature-loaded emergency torch from COAST. The torch is incredibly bright on high — 1500 lumens — and features a dial to control the brightness levels, with the ability to run for 140 hours on the lowest brightness setting.

The EAL22R is rated IP54 storm proof and built for any situation; with a tough, drop-proof nylon body, polycarbonate dome and globe construction. Users can remove the globe to allow for higher lumen output — and with carabiners on the top and bottom, the lantern can be hung to provide overhead lighting with ease.

This Torch uses either lithium or alkaline power, and can be recharged either in or out of the torch using a micro USB, and can power out to charge phones or accessories in emergency situations.

- 1500 lumens with a 140-hour runtime on low
- Sturdy control dial allows for easy brightness adjustment
- Dual power capability running on 3 x D cell batteries (sold separately) or ZITHION™ rechargeable battery (included).





EAL22R EMERGENCY AREA TORCH



DUAL POWER

ZITHION™Rechargeable — Also works with Alkaline batteries





USB POWER OUT (ON BACK)

BRIGHTNESS CONTROL LEVER

> TOUGH Poly Casing

INTEGRATED Carabiner



FOLDABLE Handle




POWER SWITCH + BATTERY LIFE INDICATOR













INSTRINSICALLY SAFE TECH

I-SAFE"

COAST Introduces New "I-Safe" Line of Intrinsically-Safe LED Torches

The HZ040 is COAST's I-Safe Torch with focusing capabilities and three mode options for max versatility in Ex ZONE 0 hazardous environments.

Users can toggle through high, low, and strobe settings. The brightest setting puts out 165 lumens. The torch features a rotary power switch to toggle through the settings, and can lock to stay on or off, at the needed brightness level.

The HZ040 also features a removable belt clip and a lanyard with an attached key to open and close/tighten the battery cavity.

- 165 lumens with rechargeable cell and up to 165 meter beam distance
- Runtime (High): 8h 15min; Runtime (Low): 37h
- Length: 7.2 in / 18.3 cm; Weight: 8.5 oz. / 240 g
- 4 x AA batteries

*About ZONE 0

ZONE 0 is classified as an environment in which an explosive gas/vapor atmosphere is continuously present or present for long periods of time. Typical ZONE 0 environments are oil and gas production and processing plants, petrochemical and chemical processing plants, gas pipelines, or re-fueling stations.








HZ040 SAFETY-RATED TORCH













INSTRINSICALLY SAFE TECH

I-SAFE"

COAST Introduces New "I-Safe" Line of Intrinsically-Safe LED Torches

The HZ050 is COAST's I-Safe Torch with five beam options for max versatility in Ex ZONE 0 hazardous environments.

Users can toggle through the following light settings: spot beam, flood beam, side beam, spot & flood beam, and spot & side beam. The brightest setting, spot & side beam, produces a 270-lumen output.

The torch features a belt clip with a magnet embedded to affix to metal surfaces. It also has a lanyard with an attached key to open and close/tighten the battery cavity. The torch also has a handy TPR grip and a tough outer to hold up to abuse.

- 270 lumens on spot + side beam and up to 89-meter beam distance
- Runtime (High): 7h 30min
- Length: 7.52 in / 19.1cm / Weight: 8.1 oz. /230 g
- 3 x AA batteries

*About ZONE 0

ZONE 0 is classified as an environment in which an explosive gas/vapor atmosphere is continuously present or present for long periods of time. Typical ZONE 0 environments are oil and gas production and processing plants, petrochemical and chemical processing plants, gas pipelines, or re-fueling stations.



HZ050 SAFETY-RATED TORCH

SAFETY RATINGS



Sas: II 1G Ex ia op is IIC T3 Ga Mine: I M1 EX ia op is I Ma











HZ025

INSTRINSICALLY SAFE TECH

I-SAFE"

COAST Introduces New "I-Safe" Line of Intrinsically-Safe LED Torches

The HZ025 is COAST's I-Safe Head torch with six beam options for max versatility in Ex ZONE 0 hazardous environments.

Users can toggle through spot beam, red beam, high and low flood beams, and high and low spot & flood beams. In the high spot & flood mode, the head torch has a max 230-lumen output. The head torch has two switches to toggle through the modes and the torch can tilt and adjust to different angles.

The HZ025 also has two strap options, one reflective cloth strap and a silicone strap for use on a hardhat. The top strap is removable and features an attached key to open or close/tighten the battery cavity.

- 230 lumens and up to 160 meter beam distance
- Runtime (High): 7h 45min; Runtime (Low): 22h
- Length: 7.52 in / 19.1cm / Weight: 10.2 oz. /230 g
- 3 x AA batteries

*About ZONE 0

ZONE 0 is classified as an environment in which an explosive gas/vapor atmosphere is continuously present or present for long periods of time. Typical ZONE 0 environments are oil and gas production and processing plants, petrochemical and chemical processing plants, gas pipelines, or re-fueling stations.



HZ025 SAFETY-RATED HEAD TORCH

SAFETY RATINGS



SILICONE + FABRIC Replaceable Strap

KEY FOR BATTERY ENCLOSURE

















STATIC-DISSIPATIVE BODY MATERIALS

WITH NON-SLIP OVER-MOLD









POWER SOURCES (INCLUDED): Q 3 x AA ALKALINE

