

ATQ

Time-Delay Midget Fuses

MIDGET, PC MOUNT & MINIATURE FUSES

MF



Amp-Trap® ATQ midget time-delay fuses are rated a full 500 volts AC with 42 ampere ratings from 1/10 to 30A. They are an excellent choice for supplemental protection of circuits up to 30A where the available short circuit current does not exceed 10,000A. (Not for Branch Circuit Protection).

FEATURES/BENEFITS:

- Numerous ratings for a wide variety of applications up to 500VAC
- Time-delay (12 seconds at 200% rating) for circuits with high inrush current
- Can be used with UltraSafe™ Fuse holders
- 1 1/2" x 13/32" (10 mm x 38 mm) dimensions

CATALOG NUMBERS (AMPS)

| | | | | | | |
|-----------|---------|-----------|-----------|-----------|----------|-------|
| ATQ1/10 | ATQ3/10 | ATQ1-1/8 | ATQ2 | ATQ3-2/10 | ATQ6 | ATQ12 |
| ATQ1/8 | ATQ4/10 | ATQ1-1/4 | ATQ2-1/8 | ATQ3-1/2 | ATQ6-1/4 | ATQ14 |
| ATQ15/100 | ATQ1/2 | ATQ1-4/10 | ATQ2-1/4 | ATQ4 | ATQ7 | ATQ15 |
| ATQ3/16 | ATQ6/10 | ATQ1-1/2 | ATQ2-1/2 | ATQ4-1/2 | ATQ8 | ATQ20 |
| ATQ2/10 | ATQ8/10 | ATQ1-6/10 | ATQ2-8/10 | ATQ5 | ATQ9 | ATQ25 |
| ATQ1/4 | ATQ1 | ATQ1-8/10 | ATQ3 | ATQ5-6/10 | ATQ10 | ATQ30 |

RECOMMENDED FUSE BLOCKS for Midget (10x38mm) Fuses

| Number of Poles | Catalog Number | | | |
|-----------------|-----------------------------------|-----------------|--------------------------|----------------------|
| | UltraSafe™ Indicating Fuse Holder | Screw Connector | Pressure Plate Connector | Copper Box Connector |
| Adder | | 30310 | 30320 | 30350 |
| 1 | USM1I | 30311 | 30321 | 30351 |
| 2 | USM2I | 30312 | 30322 | 30352 |
| 3 | USM3I | 30313 | 30323 | 30353 |
| 3 | USFM10I | | | |

RATINGS:

- **Volts:** 500VAC
- **Amps:** 1/10 to 30A
- **I.R.:** 10kA I.R.

HIGHLIGHTS:

- Time-delay

APPLICATIONS:

- Supplemental protection of lighting, solenoid, motor and transformer circuits

APPROVALS:

- UL listed to standard 248-14 File E33925
- CSA Certified to Standard C22.2 No. 248.14

