

INTRODUCTION

Are you still looking for a low cost thermometer? Did you get one? Aha! Here it is! This is a new waterproof digital thermometer with display. It is suitable for greenhouse, fish tank, swimming pool and other application scenarios which require temperature measurement. It is completely waterproof to a depth of one meter for long time. And it can continuously work for half the year with only 2 AG13 button cell.



Application:

- Vehicle temperature measurement
- Indoor temperature measurement
- Fridge temperature measurement
- Body temperature measurement
- Fish Tank/ Swimming Pool temperature measurement

SPECIFICATION

- Temperature Measurement Range: $-50^{\circ}\text{C} \sim 110^{\circ}\text{C}$
- Temperature Measurement Error: $\pm 1^{\circ}\text{C}$
- Resolution: 0.1°C
- Refresh Rate: 1.5 ~ 2 seconds
- Operating Voltage: 2x AG13 button cells
- Operating current: 4 μA (Max)
- Probe Cable Length: 1 m
- probe length: 20 mm (1 meters waterproof probe)
- Operating Temperature: $0^{\circ}\text{C} \sim 50^{\circ}\text{C}$

- Storage temperature: - 10°C ~ 60°C
- Dimension: 4.8 * 2.8 * 1.5 cm/ 1.89 * 1.1 * 0.59 inches
- Weight: 28g

SHIPPING LIST

- Digital Thermometer x1
- AG13 button cell x2