

Technical data sheet · Cablefix® Vario

Feed-through for all prefabricated cables and wires with connectors



Cable fittings and accessories

| | | |
|-----------------------|----------|--------|
| Identification | Type | BL7 |
| | Part-No. | 606253 |

Use/Area of application

| | |
|-------------|--|
| Application | <ul style="list-style-type: none">• Electrotechnology, pneumatics, hydraulics, robotics, general machine and plant construction |
| Properties | <ul style="list-style-type: none">• Feed through and terminal frames from high-quality solid• Aluminium or polyamide GF30 with additional inner brass reinforcement• High flexibility in the application• Additional mounting to existing installation easily possible• Even pressure effect on the feed through round material yields good strain relief and sealing• Unneeded holes in the module can simply sealed with blank plugs• Compact design i.e. space-saving• 2 module sizes with slot and suspension principle• Very good weathering resistance• Resistant to UV radiation, ozone, oils, fuels, acids, bases, solvents and sea water |

Technical data

| | |
|-------------------|-------------------|
| Burning behaviour | Flame-retardant |
| Temperature range | -40 °C to +135 °C |
| Protection class | IP 65 |

10.05.2007 – Subject to technical modification

Part-No. 606253

USA: LUTZE INC.

13330 South Ridge Drive • Charlotte, NC 28273, USA

Tel. +1-704-504-02 22 • Fax +1-704-504-02 23

www.lutze.com • info@lutze.com

United Kingdom: LÜTZE Ltd.

Unit 4, Brabazon Court • Borman

Lichfield Road Industrial Estate • GB-Tamworth, Staffordshire B79 7TA

Tel. +44-18 27-3 13 33-0 • Fax +44-18 27-3 13 33-2

www.lutze.com • sales.gb@lutze.co.uk



Systematic Technology

Technical data sheet · Cablefix® Vario

Feed-through for all prefabricated cables and wires with connectors

| | |
|--------------|--|
| Module type | VG=40×43.5 VK=40×22.9 for cable and wire diameters from 4 mm to 34.5 mm, see ordering information frame sizes, see ordering information |
| Maße (L×H×T) | 30 |
| Diameter | 7.0 |

Design

| | |
|--------|----------|
| Length | 30.00 mm |
|--------|----------|

General data

| | |
|-----------------------|---|
| VE | 50 piece |
| suitable for Part-No. | 606154 |
| Note | Unit corresponds to the number of required rubber modules type VK or VG |

10.05.2007 – Subject to technical modification

Part-No. 606253

USA: LUTZE INC.

13330 South Ridge Drive · Charlotte, NC 28273, USA

Tel. +1-704-504-02 22 · Fax +1-704-504-02 23

www.lutze.com · info@lutze.com

United Kingdom: LÜTZE Ltd.

Unit 4, Brabazon Court · Borman

Lichfield Road Industrial Estate · GB-Tamworth, Staffordshire B79 7TA

Tel. +44-18 27-3 13 33-0 · Fax +44-18 27-3 13 33-2

www.lutze.com · sales.gb@lutze.co.uk



Systematic Technology