

Weller®

1595TF

Product no.: 1595TF

Cutting head for 1500BSF pneumatic cutter, hard metal blades



Pointed head, flush cut



same characteristics as handtool 595TF

source images

The Perfect Cut - Strong, sharp and precise, every time

1500 Weller Erem pneumatic side cutters are light and precise. Thanks to a selection of different cutting heads they can operate extremely versatile. The cutters are suitable for cutting conventional components, soft metals or small plastic parts. The cutting heads can be interchanged easily.

THE PERFECT CUT

Strong, sharp and precise - every time

+ 1 Million Movements
Magic Spring™ design enables maximum durability with constant spring force movements

+ Quality
Uncompromising Swiss quality created to be strong, durable and sharp

+ Precision
Experience precise cuts from the high-precision screw joint that enables a smooth action with no jaw overlap

+ Strong and Sharp
Hand-crafted cutting edges for superior strength and sharpness

+ Comfort, Security and Grip
Ergonomically-shaped handles provide superior comfort and fatigue-free handling with Maximum Opening Stop Technology

ESD Safe
Made from ESD-safe material to prevent damage to sensitive components

Swiss Made

weller-tools.com **Weller**
Erem®





Technical Data

Length mm	69
Length of cutting edges mm	10
Head width mm	11
Head thickness mm	6
Head length mm	18
Max. cutting capability – hard wire mm	0.6
Weight in oz	1.171
Length of cutting edges Inches	0.394
Head width Inches	0.433
Head thickness Inches	0.236
Head length Inches	0.709
ESD-safe	on
Cut	Flush
Max. cutting capability – medium hardness mm	0.8
Max. cutting capability – copper wire mm	1.5
Length inches	2.717
Weight in g	33.2
Erem applications	Microelectronic